



Connectors > Connector Accessories > Connector Strain Relief > Ribbon Cable Connector: Pull Loop



Strain Relief Accessory Type: **Pull Loop**

Primary Product Material: **PVC**

Primary Product Color: **Natural**

Packaging Method: **Box & Carton**

Packaging Quantity: **250**

[All Ribbon Cable Connector: Pull Loop \(10\)](#)

Features

Product Type Features

Strain Relief Accessory Type	Pull Loop
------------------------------	-----------

Body Features

Primary Product Material	PVC
Primary Product Color	Natural

Dimensions

	.88 in
--	--------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	CSA LR7189, UL E28476

Packaging Features

Packaging Method	Box & Carton
Packaging Quantity	250



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1658624-4  
20 NOVO DUAL 30DP, LEAD FREE



TE Part # 2-111623-2  
26, 2MM, POL,30 DP, LEAD FREE



TE Part # 2-1658527-3  
622-2030LF=FSKT IDC S 20 30AU



TE Part # 1658620-4  
20 NOVO MIL 15DP, LEAD FREE





TE Part # 2-111623-7  
024 2MM CTR 30DP FT




TE Part # 1658621-4  
20 NOVO MIL/CTR 15DP,LEAD FREE

Customers Also Bought



TE Part #10220685-00  
CHPG-100K +/- 2% B 4075 +/- 1% BT63-H



TE Part #211903-1  
CMC DUST CAP ASSM SIZE 22



TE Part #531230-2  
SHUNT, .200 C/L,LP,2 POS, 15AU



TE Part #1-499252-2  
030 STRAIN RELIEF A-L RCPT



TE Part #4525DO-TP3AJ030APF  
PRESS XDCR,DIGITAL,PSI RANGE



TE Part #1-6609021-2  
10VB6=F7353 S0




TE Part #6609103-5  
PE0S0DH3B=C1220



TE Part #350981-2  
RING 18-14 AWG PTPBR



TE Part #1658622-7  
30 NOVO MIL/CTR 30DP,LEAD FREE



TE Part #GA23K3CG595  
CHPC-TAIWAN GOLD CHIP

Documents

Product Drawings

PULL LOOP, CUT LENGTH .88 IN

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_5088450-5\_O.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_5088450-5\\_O.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5088450-5\\_O.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ribbon Cable Interconnect Solutions](#)

English

Product Specifications

[Application Specification](#)

English