




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**  
Connector & Housing Type: **Receptacle**  
Termination Method to Wire & Cable: **Crimp**  
Connector System: **Wire-to-Board, Wire-to-Wire**  
Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	22
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Type	Receptacle
--------------	------------



Contact Retention Within Housing	Without
----------------------------------	---------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Material	Nylon 6/6
Centerline (Pitch)	4.2 mm[.165 in]

Dimensions

Row-to-Row Spacing	4.2 mm[.165 in]
Connector Width	19.8 mm[.779 in]
Connector Height	11.7 mm[.461 in]
Connector Length	47.4 mm[1.866 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	208567
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	500
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-1586000-2  
22P FH PLUG VAL-U-LOK V2




TE Part # 2-1969599-2  
22P PM PLUG VAL-U-LOK V2




TE Part # 2-794953-2  
22P PM PLUG VAL-U-LOK V2


Customers Also Bought




TE Part #1734723-1  
RJ11,6P6C,SINGLE,DIP,W/O LED 6u"




TE Part #3-1393247-4  
W31-X2M1G-2=W23/W31



TE Part #1-1969597-0  
10P RCPT VAL-U-LOK V2



TE Part #1-794954-8  
18P RCPT VAL-U-LOK V2



TE Part #2-1969597-0  
[20P RCPT VAL-U-LOK V2](#)




TE Part #3-1393247-2  
[W31-X2M1G-10=W23/W31](#)



TE Part #5-2176088-6  
[RP 1J 0.166W 3K32 0.1% 25PPM 1K RL](#)



TE Part #640389-4  
[04P MTA156 HDR ASSY SQ R/A F/L](#)



TE Part #640389-2  
[02P MTA156 HDR ASSY SQ R/A F/L](#)



TE Part #4-1393247-2  
[W31-X2M1G-5=W23/W31](#)

Documents

Product Drawings

[22P RCPT VAL-U-LOK V2](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1969597-2\\_A\\_c-2-1969597-2-a.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1969597-2\\_A\\_c-2-1969597-2-a.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1969597-2\\_A\\_c-2-1969597-2-a.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773730-3 VAL-U-LOK Connectors with TPA Flyer](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)



English

[Agency Approvals](#)

[UL Report](#)

English