




Connectors > Modular Jacks & Plugs > Industrial Mini I/O Connectors > Mini I/O Recepticle Kit Type 1 Piercing



Modular Jacks & Plugs Products: **Industrial Mini I/O**

Connector Contact Density: **High**

Modular Connector Style: **Receptacle**

Shielded: **Yes**

Performance Category: **Cat 5e**

[All Mini I/O Recepticle Kit Type 1 Piercing \(3\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Modular Jacks & Plugs Products	Industrial Mini I/O
Modular Connector Style	Receptacle
Connector System	Cable-to-Cable
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	8
Port Matrix Configuration	1 x 1
Connector Contact Density	High
Number of Loaded Positions	8

Signal Characteristics

Data Rate	10 Mb/s, 100 Mb/s, 1000 Mb/s
-----------	------------------------------

Body Features



Shield Material	Copper Alloy
Shield Plating Material	Nickel

Contact Features

Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	1.5 A

Mechanical Attachment

Panel Mount Feature	With
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Color	Black
Centerline (Pitch)	1.27 mm[.05 in]
Housing Material	Thermoplastic

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
Shielded	Yes

Industry Standards

UL Flammability Rating	UL 94V-0
Performance Category	Cat 5e

Packaging Features


Packaging Method	Blister Pack
------------------	--------------

Other

Field Serviceable	No
-------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2350304-1
MINI IO CONN Cat5e FI 2x2 AWG24 /26 T I

TE Part # 2350323-1
MINI IO CONN Cat5e FI 2x2 AWG22 T I

TE Part # CAT-IN291-M6641M
Mini I/O Field Installable Type 1

TE Part # 2201855-3
MINI I/O PLUG KIT TYPE I LM MIX

TE Part # 1-2350323-1
MINI IO CONN Cat5e FI 2x2 AWG22 T I

TE Part # 1-2350310-1
MINI IO CONN Cat6A FI 4x2 AWG24 /26 T I

TE Part # 2229737-2
MINI I/O PIERCING TYPE HAND TOOL

TE Part # 1-2350304-1
MINI IO CONN Cat5e FI 2x2 AWG24 /26 T I



TE Part # 2069772-3
MINI I/O PLUG KIT LOCK EXT.
ORANGE 100PC

TE Part # 2350310-1
MINI IO CONN Cat6A FI 4x2 AWG24
/26 T I

Customers Also Bought

TE Part #1971151-2
D1500 Junction Box 34P, V Mount type

TE Part #CAT-D9934-A83A
DYNAMIC 5000 REC AND TAB HSG

TE Part #1318697-2
DYNAMIC D-5 SERIES REC CONTACT

TE Part #1-1827863-5
DYNAMIC 1100D REC HSG 30P X
BLACK

TE Part #1376807-2
DYNATAP CONN. 18P ASSY -DYNAMI

TE Part #2295205-1
THERMOCOUPLE CONNECTOR.
STRAIN RELIEF.

TE Part #T3110009902-000
HMN-DM

TE Part #T1420100000-001
H10B-AG-BO

TE Part #2229498-1
PROXMAG SENSOR 2 PSA102-T120-
L1200-0

Documents

Product Drawings

MINI I/O REC KIT TYPE I LM MIX

English

CAD Files

Customer View Model

ENG_CVM_CVM_2201864-3_B.3d_stp.zip

English

Customer View Model



[ENG_CVM_CVM_2201864-3_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2201864-3_B.3d_igs.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773733-2_MINI_IO_FIELD_INSTALLABLE_FLYER](#)

English

[1-1773733-2_MINI_IO_FIELD_INSTALLABLE_FLYER](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English