



Connectors > PCB Connectors > PCB Headers & Receptacles > Header Assembly: Wire-to-Board, 5A, gold or tin plated



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **6**

Number of Rows: **2**

[All Header Assembly: Wire-to-Board, 5A, gold or tin plated \(89\)](#)

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	6
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Body Features

Primary Product Color	Yellow
-----------------------	--------



Contact Features

Contact Mating Area Plating Material Thickness	.38 µm[15 µin]
Mating Tab Width	.7 mm[.028 in]
PCB Contact Termination Area Plating Material Thickness	2 µm[78.73 µin]
Contact Shape & Form	Rectangular
Contact Mating Area Length	3.6 mm[.141 in]
Contact Base Material	Copper Alloy
Mating Tab Thickness	.5 mm[.02 in]
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Pin
Contact Current Rating (Max)	5 A

Termination Features

Termination Post & Tail Length	3.05 mm[.12 in]
Square Termination Post & Tail Dimension	.5 mm[.02 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention	With
Mating Alignment Type	Keyed
PCB Mount Retention Type	Retention Leg
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Polyester GF
------------------	--------------

Centerline (Pitch)	2.5 mm[.099 in]
--------------------	-----------------

Dimensions

Row-to-Row Spacing	3.3 mm[.129 in]
Connector Width	11.3 mm[.444 in]
PCB Thickness (Recommended)	1.0 – 1.6 mm[.039 – .062 in]



Connector Height	12.45 mm[.490 in]
Connector Length	10.1 mm[.397 in]

Packaging Features

Packaging Quantity	46
Packaging Method	Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-1939028-3  
DYNAMIC 1200D REC HSG 6P X  
YELLOW

Also in the Series | Dynamic 1000 Series

Connector Contacts(40)

Connector Hardware(3)

Insertion & Extraction Tools(2)

PCB Headers & Receptacles(169)

Power Contacts(9)

Rectangular Power Connectors(111)

Wire-to-Board Headers & Receptacles (169)

Customers Also Bought

TE Part #1379101-2  
COV+LEV MQS 18W 90DEG WHI

TE Part #104480-7  
SHORT POINT RECP CONT LP

TE Part #293009-1  
4 POS. FASTIN-FASTON CONN. TAB HOUSING R


TE Part #1393260-1  
SR6B4005 - V23050-A1005-A542

TE Part #1986723-3  
STR PLUG SPRING TYPE RH 3P, 3.50 mm

TE Part #1-776261-4  
14POS,PIN DIA 1.3,HDR ASSY, 180DEG,COD 4

TE Part #2005511-5  
SQUIB AK2 COVER HSG

TE Part #2103191-5  
CAP SUBASSY, KEY E, HVA280-2PHI



Documents

Product Drawings

DYNAMIC 1200D HDR ASSY V 6P X YLW GOLD

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-1939261-3\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-1939261-3\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-1939261-3\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English