



739-8442

Data Sheet

ENGLISH

RS stock number : 739-8442
Type of tool : Mini 3/8" Ratchet
Power source : Compressed air
Maximum permissible operating pressure : 90 psi (6.2 bar)
Recommended operating pressure : 90 psi (6.2 bar)

Features

Palm size Ratchet allows the operator to reach small areas
Compact and lightweight design allows maximum operator control and performance
Rear exhaust to keep airflow away from work area
High power motor for consistent performance

Specifications

Anvil Size: 3/8"
Max Torque: 34Nm / 25ft-lb
Free Speed: 300RPM
Weight: 0.49kgs
Length: 5.08" / 128mm
Min Hose Size: 3/8" / 10mm
Air inlet thread: 1/4
Sound: 80dBA
Vibration: 4.31m/s²
Ave Air Consumption: 1.8cfm / 50l/min
Recommended lubrications: 10 Weight SAE Oil

739-8442

Mini 3/8" Ratchet

Technical Data



Declaration of Conformity

We	RS Components Ltd
declare under our sole responsibility that the	739-8442 – Mini 3/8" Ratchet
conforms with the directive and the standards	2006/42/EEC EN 792-6 ISO 28927