



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Ferrule**

Primary Product Material: **Brass**

Primary Product Color: **Violet**

Packaging Method: **Bag**

Features

Product Type Features

Compatible With RF Cable Type	RG 196A
Strain Relief Accessory Type	Ferrule

Body Features

Primary Product Plating Material	Zinc
Primary Product Material	Brass
Primary Product Color	Violet

Dimensions

Compatible Insulation Diameter Range	.84 – 1.5 mm[.033 – .059 in]
--------------------------------------	------------------------------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #87175-8
03 LOCKING CLIP HSG SR .100CL




TE Part #535071-4
048 EURO TYPE C RECEPT ST ASSY




TE Part #7574442007
RAYRIM-NR8-0-STK




TE Part #87165-1
LOCKING CLIP ASSY .025 SQ LP




TE Part #1617150-8
JMGSCD-26LW = M39016/42-052L



TE Part #12331-22
CONT PIN (182-0441-22)



TE Part #292303-4
Std USB Type A, R/A, T/H



TE Part #5747844-5
09 MSFL RCPT RA 318 (SL,FM,BL)





TE Part #87175-2
[01 LOCKING CLIP HSG SR .100CL](#)

TE Part #2-1617004-5
[B07D392BZ1-0291 = RELAY.](#)

Documents

Product Drawings

[T-SHIELD,.033-.059](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_329331_V.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_329331_V.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_329331_V.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1307191 RF Coax Products Catalog](#)

English