

Datasheet

Nevada 40 Dehumidifier

RS Stock No 842-8178 (Euro Plug)

RS Stock No 839-5261 (UK Plug)



At 22 inches high the Nevada 40 is designed to be robust and easy to service.

Weights only 23kg. Built in Easy Carry Handle.

Outlet stub to fit standard hose

Autopump function which can pump water 5.4m (16ft) vertically

Easy pullout drip tray

Quiet Operation.

Can operate down to 0 degrees C

Easy adjustable timer

Unique pop-out drip tray feature to allow rapid and easy cleaning

(blocked drip trays are the most common cause of leakage)

Case easily removed to give access to all parts.

Wide fin spaced coil blocks help to prevent coil clogging and thus deliver designed performance over longer periods.

Technical Details

Dimensions: (H) 550mm (140 320mm (0)400mm. Weight:23kg. Air low (average): 120cfm.

Electricity consumption: 1.1 amp (at 60% R.H., 15 / 20°C)

Water removal: Maximum extraction rate 38.01 litres / 24 hours. Compressor: Reciprocating. Refrigerant: R134A.

Operating range: 5°C - 30°C. Cable length: 2.5m. Voltage:230v 50HZ.

Housing: Commercial quality powder coated housing resists rust and damage. Sound level @ 3m : 63 dBa