



Main

Range of product	Acti9
Device short name	iATL4
Product or component type	Step by stel control auxiliary
[Uc] control circuit voltage	230 V AC 50/60 Hz impulse 50 ms






Complementary

[Ui] rated insulation voltage	440 V
[Uimp] rated impulse withstand voltage	4 kV
Remote control type	Push-button
Step sequences	1st impulse - TL1 on, TL2 off 3rd impulse - TL1 on, TL2 on 4th impulse - TL1 off, TL2 off 2nd impulse - TL1 off, TL2 on
Mounting mode	Fixed, between 2 TL
Mounting support	DIN rail
9 mm pitches	4
Height	86 mm
Width	36 mm
Depth	71 mm
Colour	White
Connections - terminals	Tunnel type terminals 0.5...4 mm ² - rigid Tunnel type terminals 0.5...4 mm ² - rigid - with cable end Tunnel type terminals 1...4 mm ² - flexible Tunnel type terminals 1...4 mm ² - flexible - with cable end
Wire stripping length	11 mm
Tightening torque	1 N.m
Range compatibility	Acti 9 Acti9 iTL iTL Acti 9 Acti9 iTL iTLi Acti 9 Acti9 iTL iTLs Acti 9 Acti9 iTL iTLc
Product compatibility	ITL (32 A) ITL (16 A)

Environment

Overvoltage category	III
IP degree of protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C
Standards	EN/IEC 60669-2-2

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins