

LC1D1506T7

TeSys D contactor - 3P(3 NO) - AC-3 - ≤ 440 V
150 A - 480 V AC 50/60 Hz coil



Main

| | |
|---|--|
| Range | TeSys |
| Product name | TeSys D |
| Product or component type | Contacteur |
| Device short name | LC1D |
| Contacteur application | Motor control Resistive load |
| Utilisation category | AC-1 AC-3 |
| Poles description | 3P |
| Pole contact composition | 3 NO |
| [Ue] rated operational voltage | ≤ 1000 V AC 25...400 Hz for power circuit ≤ 300 V DC for power circuit |
| [Ie] rated operational current | 200 A (≤ 60 °C) at ≤ 440 V AC AC-1 for power circuit 150 A (≤ 60 °C) at ≤ 440 V AC AC-3 for power circuit |
| Motor power kW | 100 kW at 660...690 V AC 50/60 Hz 40 kW at 220...230 V AC 50/60 Hz 75 kW at 1000 V AC 50/60 Hz 75 kW at 380...400 V AC 50/60 Hz 90 kW at 500 V AC 50/60 Hz 80 kW at 415...440 V AC 50/60 Hz |
| Motor power hp | 40 hp at 200/208 V AC 50/60 Hz for 3 phases motors 50 hp at 230/240 V AC 50/60 Hz for 3 phases motors 100 hp at 460/480 V AC 50/60 Hz for 3 phases motors 125 hp at 575/600 V AC 50/60 Hz for 3 phases motors |
| Control circuit type | AC 50/60 Hz |
| Control circuit voltage | 480 V AC 50/60 Hz |
| Auxiliary contact composition | 1 NO + 1 NC |
| [Uimp] rated impulse withstand voltage | 8 kV conforming to IEC 60947 |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 200 A at ≤ 60 °C for power circuit |
| Irms rated making capacity | 1660 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 |
| Rated breaking capacity | 1400 A at 440 V for power circuit conforming to IEC 60947 |
| [Icw] rated short-time withstand current | 100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit 250 A ≤ 40 °C 10 min power circuit 580 A ≤ 40 °C 1 min power circuit 1200 A ≤ 40 °C 10 s power circuit 1400 A ≤ 40 °C 1 s power circuit |
| Associated fuse rating | 250 A gG at ≤ 690 V coordination type 2 for power circuit 315 A gG at ≤ 690 V coordination type 1 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|--|--|
| Average impedance | 0.6 mOhm at 50 Hz - Ith 200 A for power circuit |
| [U _i] rated insulation voltage | 1000 V for power circuit conforming to IEC 60947-4-1 600 V for power circuit certifications CSA 600 V for power circuit certifications UL 690 V for signalling circuit conforming to IEC 60947-1 600 V for signalling circuit certifications CSA 600 V for signalling circuit certifications UL |
| Electrical durability | 0.85 Mcycles 150 A AC-3 at U _e ≤ 440 V 1 Mcycles 200 A AC-1 at U _e ≤ 440 V |
| Power dissipation per pole | 24 W AC-1 13.5 W AC-3 |
| Protective cover | With |
| Mounting support | Plate Rail |
| Standards | EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 CSA C22.2 No 14 |
| Product certifications | BV CCC CSA DNV GL GOST RINA UL LROS |
| Connections - terminals | Power circuit : bars 15 x 25 mm Control circuit : lugs-ring terminals - external diameter: 8 mm Power circuit : lugs-ring terminals - external diameter: 25 mm |
| Tightening torque | Control circuit : 1.2 N.m - on lugs-ring terminals - with screwdriver flat Ø 6 mm screw : M3.5 Control circuit : 1.2 N.m - on lugs-ring terminals - with screwdriver Philips No 2 screw : M3.5 Power circuit : 12 N.m - on lugs-ring terminals hexagonal 13 mm screw : M8 Power circuit : 12 N.m - on bars hexagonal 13 mm screw : M8 |
| Operating time | 20...35 ms closing 40...75 ms opening |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical durability | 8 Mcycles |
| Operating rate | 1200 cyc/h at ≤ 60 °C |

Complementary

| | |
|---------------------------------|--|
| Coil technology | Built-in bidirectional peak limiting diode suppressor |
| Control circuit voltage limits | 0.3...0.5 U _c at 55 °C drop-out 50/60 Hz 0.8...1.15 U _c at 55 °C operational 50/60 Hz |
| Inrush power in VA | 280...350 VA at 20 °C (cos φ 0.9) 60 Hz 280...350 VA at 20 °C (cos φ 0.9) 50 Hz |
| Hold-in power consumption in VA | 2...18 VA at 20 °C (cos φ 0.9) 60 Hz 2...18 VA at 20 °C (cos φ 0.9) 50 Hz |
| Heat dissipation | 3...4.5 W at 50/60 Hz |
| Auxiliary contacts type | Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1 Type mirror contact (1 NC) conforming to IEC 60947-4-1 |
| Signalling circuit frequency | 25...400 Hz |
| Minimum switching current | 5 mA for signalling circuit |
| Minimum switching voltage | 17 V for signalling circuit |
| Non-overlap time | 1.5 ms on de-energisation (between NC and NO contact) |

1.5 ms on energisation (between NC and NO contact)

Insulation resistance > 10 MOhm for signalling circuit

Environment

| | |
|---|---|
| IP degree of protection | IP2x front face conforming to IEC 60529 |
| Protective treatment | TH conforming to IEC 60068-2-30 |
| Pollution degree | 3 |
| Ambient air temperature for operation | -5...60 °C |
| Ambient air temperature for storage | -60...80 °C |
| Permissible ambient air temperature around the device | -40...70 °C at U _c |
| Operating altitude | 3000 m without derating in temperature |
| Fire resistance | 850 °C conforming to IEC 60695-2-1 |
| Flame retardance | V1 conforming to UL 94 |
| Mechanical robustness | Vibrations contactor open 2 Gn, 5...300 Hz Vibrations contactor closed 4 Gn, 5...300 Hz Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 6 Gn for 11 ms |
| Height | 158 mm |
| Width | 120 mm |
| Depth | 136 mm |
| Product weight | 2.5 kg |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Not Green Premium product |
| RoHS | Compliant - since 0932 - Schneider Electric declaration of conformity |
| Product environmental profile | Available |
| Product end of life instructions | Available |