

400 17X19

Double ended ring spanner

open

Code	ETIM
6057780	EC002188
EAN	UNSPSC
4010886605776	27-11-17-05
Country of origin	eCl@ss
Germany	21-04-01-06
Customs tariff number	
82041100	



Article description

- Acc. to DIN 3118
- Sizes 8x10 to 12x14 mm with hexagon
- Vanadium steel 31CrV3, chrome-plated
- Application on hydraulic/brake lines
- Use:
- Heads 15° angled
- Hexagonal opening 30° offset, UD profile opening 15° offset

Article information

Contents (Qty of pieces)	1	Width of head 2 [mm]	35 mm
Version/Execution	Heads 15° angled hexagonal Opening 30° offset, UD profile Opening 15° offset	Head height 2 [mm]	13,2 mm
Net weight [kg]	0,179 kg	Head height 1 [mm]	12,2 mm
Total length [mm]	215 mm	Width of head 1 [mm]	32,0 mm
Total width [mm]	35 mm	Width across flats [mm]	17x19
Total height [mm]	18 mm	Width across flats 2 [mm]	19
Surface	chrome-plated	Ring profile	UNIT-DRIVE
Use	Application on hydraulic/brake lines	Opening width 1 (min.) [mm]	14,0 mm
Material	31CrV3	Opening width 2 (max.) [mm]	15,0 mm
Standard	DIN 3118	Weight	0,400 lbs
Width across flats 1 [mm]	17	Ring angle	15°