




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spring Spade Terminal**

Wire Size: **2050 – 5180 CMA**

Stud Size: **#5, M3**

Features

Product Type Features

Stud Size	#5, M3
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Contact Features

Spade Terminal Type	Spring Spade Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	3.18 mm [.125 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	14.63 mm [.576 in]
Barrel Inside Diameter	2.16 mm [.085 in]



Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 8-320857-1
SOLIS SPD FLG 16-14, 10




TE Part # 53833-1
SOLIS SPR SPADE 16-14 8


Customers Also Bought




TE Part #CONMCX001
MCX Jack 50 Ohm PCB Through Hole




TE Part #T4130012041-000
M12,REAR MOUNT,MALE,A,4P, SOLDER WIRE




TE Part #T4031017041-000
M8.FMLE.PNLREAR.4POS.STR




TE Part #5-103956-1
10X2 MTE RCPT SR LATCH .100CL




TE Part #1376675-1
025 PLUG HSG ASSY S/BODY 12P




TE Part #B1442N
WHIP,MC,1/2,144-174MHZ TUN,2.4, CH,NGP,




TE Part #5-103956-2
8X3 MTE RCPT SR LATCH .100CL



TE Part #CSI-SGFB-200-UFFR
SMA to U.FL/MHF1 200mm 1.13 OD



TE Part #CSI-RGFB-200-UFFR
RP-SMA to U.FL/MHF1 200mm 1.13 OD



TE Part #YS1503
YAGI,SS,3,150-174MHz, 17, 7.1dBi

Documents

Product Drawings
SOLIS SP SPD 16-14 5

English

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_53177-1_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_53177-1_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_53177-1_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English