

Rebar tying tool LXT®

DTR181

18V

Suitable for tying underfloor heating cables and rebars.

Compatible with thick rebars (D22 x D25). Can be operated single handed. Tie wire reel can be replaced simply by opening Reel cover.



Technical specifications

Nominal Battery Voltage	18 V
Brushless Motor	✓
Voltage LXT	✓
Wire diameter	0,8 mm
Maximum tying capacity 2 rebars	22 x 25 mm
Maximum tying capacity 3 rebars	(16 x 16) x 25 mm
Maximum tying capacity 4 rebars	(16 x 16) x (13 x 13) mm
Sound Power Level (L _{WA})	90 dB(A)
Sound Pressure Level (L _{pA})	82 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Tool weight with battery	2,4 - 2,7 kg
Product Dimensions (L x W x H):	317 x 93 x 318 mm

User benefits

- Brushless maintenance-free and long-life motor
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.com



Related products

Other

User manual

Parts drawing