



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.16 – 1.31 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.33 mm [.013 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.33 mm[.013 in]
Terminal Orientation	Straight Reverse
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Product Length	22.28 mm[.877 in]
Terminal Material Thickness	.33 mm[.013 in]
Wire Size	.16 – 1.31 mm²

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	2500
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1494212-2
SIZE(2.8) AMPLIVAR FASTON RECP

TE Part # 1742685-1
FASTON 187 TERMINAL-FLAG REC
18 AWG TPBR

TE Part # 1478484-2
STATOR TERMINAL

TE Part # 1494211-1
SIZE(2.8) AMPLIVAR FASTON RECP

TE Part # 1494212-1
SIZE(2.8) AMPLIVAR FASTON RECP

TE Part # 1814988-1
.250SERIES FASTIN-FASTON TAB
AMPLIVAR

TE Part # 63481-2
RCPT STATOR 21-15 0173PTPBR

Also in the Series | Special Purpose Terminals

PCB Terminals(2)

Quick Disconnects(9)

Customers Also Bought


TE Part #1742451-1
AMPLIVAR WIRE PIN 600-1400 020BRS

TE Part #794956-3
VAL-U-LOK SKT PHBZ SN 22-18AWG

TE Part #5069874011
CGPT-19/9.5-0-SP

TE Part #2-520405-2
ULTRA-FAST 250 ASY REC 22-18 TPBR






TE Part #2-520080-2

[ULTRA-FAST .110/.125 ASY REC 22-18 TPBR](#)



TE Part #1776293-2

[TSB23002DS=EUROPA TERM BLK, 8MM](#)



TE Part #137963J001

[V2-1.5-0-SP-SM](#)



TE Part #2151096-1

[OCEAN-2.0-APPLICATOR-S-062F125F-RSM](#)



TE Part #7-2151096-7

[OCEAN_2.0_SPARE_PART_KIT-062F125F](#)



TE Part #60577-1

[110 FASTON REC 22-18 AWG TPBR](#)

Documents

Product Drawings

STATOR TERMINAL

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1478484-1_D.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1478484-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1478484-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

AMPLIVAR Stator Receptacles with FASTON Mating End

English