

# VAL-SPP-T2-275-1+0-UT - Type 2 surge arrester



1466209

<https://www.phoenixcontact.com/gb/products/1466209>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in surge protective device, in accordance with type 2/class II, for 1-phase power supply networks with combined installation of PE and N in one conductor (2-conductor system: L, N/PEN).

## Your advantages

- Easy and safe installation with forward-thinking handling and safety features
- Reliable system protection with maximum performance and endurance
- Can be used in a wide range of applications due to the optimized design and broad portfolio
- Simple planning due to comprehensive digital data and selectors

## Commercial data

Item number	1466209
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL1381
Product key	CL1381
GTIN	4063151857097
Weight per piece (including packing)	143.65 g
Weight per piece (excluding packing)	121.4 g
Customs tariff number	85363030
Country of origin	DE

# VAL-SPP-T2-275-1+0-UT - Type 2 surge arrester



1466209

<https://www.phoenixcontact.com/gb/products/1466209>

## Technical data

### Notes

#### General

Note	For pollution degree 3 and wiring with fork cable lugs, an additional minimum lateral distance of 1 mm to earthed conductive surfaces must be maintained for cross-sections $\geq 16 \text{ mm}^2$ . No additional lateral distances are required for pollution degree 2.
------	--

### Product properties

Product type	Surge arrester
Product family	VAL-SPP
IEC test classification	II T2
EN type	T2
IEC power supply system	TN TT
Type	DIN rail module, two-section, divisible
Number of positions	1
Surge protection fault message	optical, remote signaling via optional module

#### Insulation characteristics

Overvoltage category	III
Pollution degree	3

### Electrical properties

Maximum power dissipation for nominal condition	$\leq 120 \text{ mVA}$
Nominal frequency $f_N$	50 Hz (60 Hz)

### Connection data

Connection method	Screw connection
Screw thread	M5
Tightening torque	3 Nm ... 3.5 Nm
Stripping length	18 mm
Conductor cross-section flexible	1.5 mm <sup>2</sup> ... 35 mm <sup>2</sup> (without ferrule) 2x 1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup> (2 conductors with the same cross-section)
Conductor cross-section rigid	1.5 mm <sup>2</sup> ... 50 mm <sup>2</sup> 2x 1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup> (2 conductors with the same cross-section)
Conductor cross-section AWG	15 ... 2
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>
Conductor cross-section, flexible, with ferrule, with plastic sleeve	1.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>

# VAL-SPP-T2-275-1+0-UT - Type 2 surge arrester




1466209

<https://www.phoenixcontact.com/gb/products/1466209>

	2x 1.5 mm <sup>2</sup> ... 10 mm <sup>2</sup> (2 conductors with the same cross-section)
Conductor cross-section flexible, with ferrule without plastic sleeve	1.5 mm <sup>2</sup> ... 25 mm <sup>2</sup>
	2x 1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup> (2 conductors with the same cross-section)
Connection method	Fork-type cable lug
Conductor cross-section flexible	1.5 mm <sup>2</sup> ... 25 mm <sup>2</sup>

## Dimensions

Dimensional drawing	
Width	17.8 mm
Height	96.6 mm
Depth	71.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	1 Div.

## Material specifications

Color	gray (RAL 7042)
	light gray (RAL 7035)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6-FR 20 % GF
	PBT
Material group	I
Housing material	PA 6.6-FR 20 % GF
	PBT

## Protective circuit

Mode of protection	L-N
	L-PEN
Nominal voltage $U_N$	240 V AC $\pm 10\%$ (TN)
	240 V AC $\pm 10\%$ (TT)
Nominal frequency $f_N$	50 Hz (60 Hz)
Maximum continuous operating voltage $U_C$	275 V AC
Rated load current $I_L$	80 A (25 mm <sup>2</sup> )
Nominal discharge current $I_n$ (8/20) $\mu$ s	20 kA
Maximum discharge current $I_{max}$ (8/20) $\mu$ s	40 kA
Short-circuit current rating $I_{SCCR}$	50 kA
Voltage protection level $U_p$	$\leq 1.35$ kV
Residual voltage $U_{res}$	$\leq 1.35$ kV (at $I_n$ )
	$\leq 1.1$ kV (at 10 kA)
	$\leq 1$ kV (at 5 kA)

# VAL-SPP-T2-275-1+0-UT - Type 2 surge arrester



1466209

<https://www.phoenixcontact.com/gb/products/1466209>

	≤ 0.9 kV (at 3 kA)
TOV behavior at $U_T$	350 V AC (5 s / withstand mode)
	460 V AC (120 min / safe failure mode)
Response time $t_A$	≤ 25 ns
Max. backup fuse with V-type through wiring	80 A (gG)
Max. backup fuse with branch wiring	315 A (gG)

## Additional technical data

Short-circuit current rating $I_{SCCR}$	100 kA
---	--------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20C (Installed)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Altitude	≤ 5000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g (Half-sine / 11 ms / 3x ±X, ±Y, ±Z)
Vibration (operation)	5g (10 ... 500 Hz / 2.5 h / X, Y, Z)

## Standards and regulations

Standards/specifications	IEC 61643-11
Note	2011
Standards/specifications	EN 61643-11
Note	2012 + A11:2018

## Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

# VAL-SPP-T2-275-1+0-UT - Type 2 surge arrester




1466209


<https://www.phoenixcontact.com/gb/products/1466209>

## Drawings

Dimensional drawing



Schematic diagram

Pollution degree	2		3	
	Altitude		Altitude	
	≤4000 m	5000 m	≤4000 m	5000 m
 ≥50 mm <sup>2</sup>	-	-	-	-
 ≥35 mm <sup>2</sup>	-	-	-	-
 ≥25 mm <sup>2</sup>	-	-	-	-
 ≥16 mm <sup>2</sup>	-	1 mm	1 mm	1 mm


Minimum lateral distance to active and grounded conductive parts

# VAL-SPP-T2-275-1+0-UT - Type 2 surge arrester




1466209

<https://www.phoenixcontact.com/gb/products/1466209>



Max. permissible current in relation to the ambient temperature

Circuit diagram



# VAL-SPP-T2-275-1+0-UT - Type 2 surge arrester



1466209

<https://www.phoenixcontact.com/gb/products/1466209>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1466209>

### **DNV**

Approval ID: TAE0000501



### **IECEE CB Scheme**

Approval ID: NL-118261

# VAL-SPP-T2-275-1+0-UT - Type 2 surge arrester



1466209

<https://www.phoenixcontact.com/gb/products/1466209>

## Classifications

### ECLASS

ECLASS-13.0	27171202
ECLASS-15.0	27171202

### ETIM

ETIM 9.0	EC000941
----------	----------

# VAL-SPP-T2-275-1+0-UT - Type 2 surge arrester



1466209

<https://www.phoenixcontact.com/gb/products/1466209>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)