

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0760010110

Status:


Active

Overview:

EXTreme ZPower Connectors

Description:

10.30mm EXTreme ZPower Connector, 10 Press-Fit Tails, Tin (Sn) Plating, for 3.18mm Thick PC Board



Series image - Reference only

Documents:	
3D Model	Application Specification AS-76001-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-76001-901 (PDF)
Product Specification PS-76001-999-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	76001
Application	Board-to-Board, Power, Wire-to-Board
Comments	Power Connector
Overview	EXTreme ZPower Connectors
Product Name	EXTreme ZPower
UPC	800756774664
Physical	
(p)ower-(s)ignal Configuration	1p - 0s
Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Durability (mating cycles max)	5
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3.889/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.90mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	2.36mm
Packaging Type	Tray
Pitch - Mating Interface	6.00mm
Pitch - Termination Interface	3.18mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Low-Halogen	
Need more information on product environmental compliance?	
Email productcompliance@molex.com	
Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

76001 Series

Use With

62100-5300 Extraction Tool

Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	50.0A
Voltage - Maximum	250V
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-76001-001-001
Packaging Specification	PK-76001-901
Product Specification	PS-76001-999-001
Sales Drawing	SD-76001-001

This document was generated on 08/27/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION