



Main

Network rated voltage	400 V AC 50 Hz 415 V AC 50 Hz
Reactive power rating	175 kvar
Operating mode	Automatic
Range	PowerLogic
Device short name	automatic capacitor bank
Product or component type	Capacitor bank

Complementary

Network pollution level	No polluted
[Gh/Sn] harmonic pollution rate	0...15 %
[THDU] total harmonic distortion of voltage	0...3 %
Power per step	25 kvar
Step composition	25 + 3x50
Location of connection	Top
Controller type	PowerLogic PFC Controller VPL6
Capacitor technology	EasyLogic PFC Capacitor
Poles description	3P
Capacitance tolerance	- 5 % to 10 %
[Ui] rated insulation voltage	690 V
[Uimp] rated impulse withstand voltage	8 kV
Maximum permissible voltage	1.1 x Un (8 hours over 24 hours) conforming to IEC 60831
[Imp] maximum permanent current	Battery: 1.36 x In at 400 V conforming to IEC 61439-2 Battery: 1.19 x In at 415 V conforming to IEC 61439-2 Capacitor: 1.5 x In at 480 V conforming to IEC 60831
Main incomer protection	Circuit breaker protection
Breaking capacity	Icu 35 kA
Control type	Rotary handle
Step protection type	Overload: harmonic control from PowerLogic PFC Controller Short-circuit: main circuit breaker
Accessibility for operation	Front
Colour	Grey (RAL 7035)
Maximum weight	131 kg
Height	1000 mm
Width	800 mm
Depth	300 mm
Provided equipment	Auxiliary transformer
Internal voltage transformer	400/230 V - 250 VA
Function available	GenSet shedding contact Alarm contact

Environment

Standards	IEC 61439-1 IEC 61921 IEC 61439-2
Product certifications	EAC[RETURN]ASEFA[RETURN]CE
Mounting location	Indoor
IP degree of protection	Environment: IP31
IK degree of protection	IK10
Relative humidity	0...95 %
Operating altitude	<= 2000 m
Ambient air temperature for operation	-5...45 °C
Average ambient air temperature for operation	35 °C (annual) 45 °C (over 24 hours)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins