

RewoMech® 640




APPLICATION

- › metal and plastics processing
- › metalworking and mechanical engineering
- › automotive and supply industry
- › cleaning and maintenance
- › metal processing
- › assembly and transportation works
- › working with oily and wet parts

QUALITIES AND ADVANTAGES

- › breathable artificial leather
- › no material hardening
- › absorbent surface profile for a sure grip
- › very good fit
- › good dexterity



Article no.	640
Name	RewoMech® 640
Material	artificial leather, polyester with spandex
Description	artificial leather palm, stretch fabric, Velcro® fastener
Length (mm)	215 - 270
Total thickness (mm)	0,7 ± 0,10
Colour	grey/black
Size	7, 8, 9, 10, 11, 12
Classification	category II EN 388:2016  2121X



FEATURES

- › free from Chromate VI
- › terry cloth material for sweat absorption
- › Velcro® fastener for a sure glove fit
- › also available as cut/puncture resistant glove art. 646

www.kcl.de
sales@kcl.de



by Honeywell

KCL GmbH

Industriepark Rhoen
Am Kreuzacker 9
36124 Eichenzell
Germany
Phone +49 6659 87-300
Fax +49 6659 87-318