




Energy & Power > Solar Connectors & Adapters > SOLARLOK PV4-S DC Crimp Connectors



Solar Connector Type: Cable Coupler

Solar Connector Style: Socket

Keying Type: Plus

[All SOLARLOK PV4-S DC Crimp Connectors \(12\)](#)

Features

Product Type Features

Solar Connector Type	Cable Coupler
Solar Connector Style	Socket

Configuration Features

Keying Type	Plus
-------------	------

Housing Features

Housing Color	Blue
Housing Material	Polycarbonate (PC)

Packaging Features

Packaging Quantity	7000
--------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-SAFE-TE
Solarlok SAFE-TE Connectors



TE Part # 2270025-1
SOCKET CONNECTOR KITS, PV4-S1F 4MM2,6MM2

Also in the Series | SOLARLOK PV4-S DC Connector



Solar Connectors & Adapters(8)

Customers Also Bought






TE Part #2309873-1
6POS,NANOMQS,REC HSG ASSY,
COD A



TE Part #2013031-2
0.50 SERIES 24POS PLUG ASSY



TE Part #1801610-1
BULK HEAD, MCON, 10W, CLIPPED



TE Part #1554289-1
0.50 CONN 40P PLUG ASSY KEYING
TYPE2



TE Part #2382569-2
32POS,NANOMQS,REC HSG,UNSLD,
COD B,STD




TE Part #2232228-1
DUST COVER FOR PV4 PIN



TE Part #353716-2
DYNAMIC D-3 TAB CONT. 3L AU 0.38



TE Part #2405887-1
0.5 SERIES,TERMINAL,0.13-0.22MM2,
SN



TE Part #2434942-1
MCON 1.2,TERMINAL,LL TAB SWS SN



TE Part #2395681-1
10POS,MQS,REC HSG ASSY,UNSLD,
COD A

Documents

Product Drawings
DUST COVER FOR PV4 SOCKET
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2232227-1_C.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_2232227-1_C.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2232227-1_C.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



SOLARLOK 2.0 DC connector

English

SOLARLOK 2.0 DC connector

German

SOLARLOK PV4-S DC CRIMP CONNECTORS

English