

Trunk line branch terminal - UDB 2X35/25 GY - 3071350

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Trunk line branch terminal, Connection method: Screw connection, Number of positions: 1, Cross section: 10 mm² - 35 mm², AWG: 8 - 2, Width: 27 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

Product Features

- The branch terminal is suitable for the simple voltage pick-off of main supply cables
- Conformance with DIN VDE 0603-2/EN 60998-1



Key commercial data

Packing unit	1 pc
Minimum order quantity	5 pc
Weight per Piece (excluding packing)	80.0 GRM
Custom tariff number	85369010
Country of origin	Germany

Technical data

General

Number of levels	1
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60998-1
Maximum load current (lower level)	125 A

Trunk line branch terminal - UDB 2X35/25 GY - 3071350

Technical data

General

Nominal current I_N (lower level)	125 A
Nominal voltage U_N	400 V (Max. 1000 V)
Additional text	Max. 1000 V
Connection in acc. with standard	IEC 60998-1
Open side panel	nein
Number of positions	1

Dimensions

Width	27 mm
Length	55 mm
Height NS 35/7,5	46 mm
Height NS 35/15	53.5 mm

Connection data

Connection in acc. with standard	IEC 60998-1
Connection method	Screw connection
Note	Use ferrules for stranded conductors
Conductor cross section solid min.	10 mm ²
Conductor cross section solid max.	35 mm ²
Conductor cross section AWG/kcmil min.	8
Conductor cross section AWG/kcmil max.	2
Conductor cross section stranded min.	10 mm ²
Conductor cross section stranded max.	25 mm ²
Min. AWG conductor cross section, stranded	8
Max. AWG conductor cross section, stranded	3
Conductor cross section stranded, with ferrule without plastic sleeve min.	10 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	10 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	16 mm ²
Stripping length	25 mm
Screw thread	M6/M8
Tightening torque, min	4 Nm
Connection in acc. with standard	IEC 60998-1
Connection method	Screw connection
Conductor cross section solid min.	1.5 mm ²
Conductor cross section solid max.	25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve min.	1.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	16 mm ²

Trunk line branch terminal - UDB 2X35/25 GY - 3071350

Technical data

Connection data

Conductor cross section stranded, with ferrule with plastic sleeve min.	1.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	10 mm ²
Stripping length	25 mm

Classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Drawings

Circuit diagram

