




Connectors > RF Connectors > Coax Connectors > BNC RF Connector: Jack, Right-Angle, 75 Ohm, 4 GHz



RF Interface: **BNC**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**

Impedance: **75 Ω**

RF Connector Coupling Mechanism: **Bayonet**

[All BNC RF Connector: Jack, Right-Angle, 75 Ohm, 4 GHz \(1\)](#)

Features

Product Type Features

RF Interface	BNC
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Right Angle
Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	75 Ω
-----------	------

Body Features

Body Material	Zinc
---------------	------



Body Plating Material	Tin
-----------------------	-----

Contact Features

RF Connector Center Contact Underplating Material	Copper, Nickel
	30 µin
RF Connector Center Contact Plating Material	Gold (Au)
RF Connector Center Contact Material	Beryllium Copper

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	4.34 mm[.17 in]

Mechanical Attachment

Panel Attachment Style	Rear Mount
PCB Mount Retention	With
RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	With

Dimensions

Mounting Post Length	4.34 mm[.171 in]
Profile Height from PCB	10.97 mm[.432 in]
RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Grade	Commercial
Dielectric Material	Polymethylpentene

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (.6% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1-106507-2
25P.HDP20 REC.ASSY.



TE Part #5148292-5
ASSY,RECEPTACLE,EUROCARD,TYPE



TE Part #1622892-1
CRG0603 1% 240R



TE Part #2299940-5
ZQSFP+ STACKED REC ASSEMBLY
2X1,HS



TE Part #5747375-8
37 PLUG SP/FMS INSRT



TE Part #640388-6
06P MTA156 HDR ASSY RN STR F/L



TE Part #6-1462037-7
IM46GR=IM RELAY 100mW 12V BIS



TE Part #2299924-3
ZQSFP+ STACKED REC ASSEMBLY 2X3, HS



TE Part #1-499786-0
050 UNIV HDR RA 4S 15DP STD L1



TE Part #6651678-1
279-1133-10200A=TA CONN,SKT, FLATPAQ

Documents

Product Drawings

JACK,RTANG,PCB,75 OHM,BNC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5415373-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5415373-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5415373-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION

Japanese

Product Specification

Japanese