## Issue E

# **QUADRATURE SPEED AND DIRECTION SENSORS, SNG-Q SERIES**

1334C L

### **GENERAL INFORMATION**

Honeywell's SNG-Q Series Quadrature Speed and Direction Sensors are designed to provide both speed and direction information. Speed information is provided from digital square wave outputs; direction is provided using a quadrature output with signals 90° phase shifted from each other. With the quadrature output, target direction is determined by output lead/lag phase shifting.

The product is designed for applications where enhanced accuracy is required to detect small target features. This accuracy is enabled by dual differential Hall-effect sensor IC technology. The SNG-Q Series is designed for a wide operating temperature range, robust electrical noise immunity and industry leading environmental sealing capability.

This product includes an O-ring seal for pressure applications, and a fixed mounting flange for simple installation using one fastener.

TABLE 1. ELECTRICAL SPECIFICATIONS			
Characteristic	Parameter	Comment	
Supply voltage	4.5 V to 26 V	_	
Output signal:			
type	square wave	Two channel, phase shifted by 90° either channel, may lead or lag.	
duty cycle <sup>1</sup>	50% ±10%	Dependent on target geometry and sensor-to-target orientation; see Figures 2, 3, 4, 5, 6, 7, 8, 9 for recommended orientation.	
phase shift	90° ±45°	Dependent on target geometry and sensor-to-target orientation; see Figures 2, 3, 4, 5, 6, 7, 8, 9 for recommended orientation.	
high	≥Vs - 0.5 V	_	
low:		_	
SNG-QPLA/QPCA/	<0.5 V		
QPMB/QPDB	<1.75 V		
load current	40 mA max.	Applies to each output at all conditions.	
rise time	10 us max.	1 kOhm pull-up resistor, dependent on load resistor.	
fall time	5 us max.	1 kOhm pull-up resistor, dependent on load resistor.	
frequency	3 Hz to 20 kHz	Frequencies >10 kHz may be dependent on target geometry and air gap.	
Short circuit protection	50 mA max.	_	
Supply current: normal max.	12 mA 18 mA	all conditions	
Reverse voltage	-26 V max.	10 min duration	

<sup>&</sup>lt;sup>1</sup>Duty cycle = Time high/time total.

TABLE 2. MECHANICAL SPECIFICATIONS			
Characteristic	Parameter		
Sensing air gap	0,0 mm to 2,0 mm [0.0 in to 0.08 in]		
Target: width¹ slot width² tooth width² tooth height³	>5,0 mm [0.20 in] recommended; 12,7 mm [0.5 in] typ. 2,0 mm [0.08 in] min. 2,0 mm [0.08 in] min. >3,0 mm [0.12 in] recommended; 5,0 mm [0.20 in] typ.		
Materials: housing bushing O-ring cable <sup>4</sup>	PBT brass fluorocarbon with PTFE coating, Ø11,8 mm [Ø0.47 in] OD x Ø1,80 mm [Ø0.07 in] CS EVA, four conductor, 36 AWG, 28 strand, Ø5,2 mm [Ø0.20 in] jacket		
Mounting: bore size <sup>5</sup> torque	Ø15,15 mm to Ø15,40 mm [Ø0.60 in to Ø0.61 in] 10 N m [88.5 in-lb] max. with M6 X 1.0 bolt		

<sup>&</sup>lt;sup>1</sup>Narrower targets may limit axial offsets.

<sup>&</sup>lt;sup>5</sup>Application dependent.

TABLE 3. ENVIRONMENTAL SPECIFICATIONS			
Characteristic	Condition	Parameter	
EMI: radiated immunity bulk current injection ESD	ISO 11452-2, 400 MHz to 1 GHz ISO 11452-4, 1 MHz to 400 MHz ISO 10605, Section 9 conforms to CE, UKCA Mark standards EN60947-5-2:2007 and EN 60947-5-2/A1:2012	100 V/m 100 mA ±8 kV contact, ±15 kV air	
Operating temperature	_	-40°C to 150°C [-40°F to 302°F]	
Thermal shock, air to air	-40°C to 150°C [-40°F to 302°F], 60 min. soak, <3 s transfer	500 cycles	
Humidity	95% humidity at 38 °C [100 °F]	240 hr	
Salt fog	5% salt solution by mass at 35 °C [95 °F]	96 hr	
Thermal saline dunk	100°C to 25°C [212°F to 77°F] air to liquid, 5% saline	10 cycles	
High temperature exposure with power	150°C [302°F], 13.5 Vdc, 1 kOhm load	500 hr	
Vibration	3 perpendicular axes, 48 hr per axis	29.28 GMS, 50 Hz to 2000 Hz MIL-STD-202-214	
Degree of protection	_	IP69K	
Resistance to fluids	_	general under-the-hood automotive fluids	

<sup>&</sup>lt;sup>2</sup>Other geometry may be suitable.

<sup>&</sup>lt;sup>3</sup>Shorter tooth heights may limit maximum air gap performance.

<sup>&</sup>lt;sup>4</sup>Applies to SNG-QPLA-001, SNG-QPCA-001, SNG-QPMB-000, SNG-QPDB-000, and SNG-QPDB-002.

### FIGURE 1. SENSOR OUTPUT (ALL CATALOG LISTINGS)

909

Tooth

(lagging)

Target cross section relative to output channel A

# Output channel A (leading) Phase shift Output channel B

180°

2709

Slot

FIGURE 2. POSSIBLE MOUNTING ORIENTATIONS






FIGURE 3. SNG-QPLA-000 MOUNTING DIMENSIONS (FOR REFERENCE ONLY: MM/[IN].)


360°

909





### FIGURE 4. SNG-QPCA-001 MOUNTING DIMENSIONS (FOR REFERENCE ONLY: MM/[IN].)





### FIGURE 5. SNG-QPRA-000 MOUNTING DIMENSIONS (FOR REFERENCE ONLY: MM/[IN].)






Note: The load resistor values should be such that the output current does not exceed the maximum load current of 40 mA.

Use Ohm's Law to calculate the load resistor based on the supply/load voltage used:

R = V / 0.04 A





AMP SUPERSEAL 1.5 CONNECTOR PINOUT (MATING CONNECTOR IS AMP			
SUPERSEAL 1.5 282088)			
Pin A	Pin B	Pin C	Pin D
Ground	Channel A	Channel B	Vsupply

SNG-QPMB-000

# **QUADRATURE SPEED AND DIRECTION SENSORS SNG-Q SERIES**

## FIGURE 6. SNG-QPMB-000 MOUNTING DIMENSIONS (FOR REFERENCE ONLY: MM/[IN].)





# V<sub>S</sub>: Yellow wire

**Circuit Diagram** 

Note: The load resistor values should be such that the output current does not exceed the maximum load current of 40 mA.

Channel A: White wire

Use Ohm's Law to calculate the load resistor based on the supply/load voltage used:


R = V / 0.04 A

Ground: Black wire


Supply (4.5 V to 26 V)

LEADWIRE ASSIGNMENT			
Yellow	Black	White	Blue
Vsupply	Ground	Channel A	Channel B

## FIGURE 7. SNG-QPDB-000 MOUNTING DIMENSIONS (FOR REFERENCE ONLY: MM/[IN].)








Note: The load resistor values should be such that the output current does not exceed the maximum load current of 40 mA.


Use Ohm's Law to calculate the load resistor based on the supply/load voltage used:


R = V / 0.04 A



#### **AMP SUPERSEAL 1.5 282106 PINOUT** (MATING CONNECTOR IS AMP SUPERSEAL 1.5 282088) Pin 1 Pin 2 Pin 3 Pin 4 Channel B Channel A Ground Vsupply

## FIGURE 8. SNG-QPDB-002 MOUNTING DIMENSIONS (FOR REFERENCE ONLY: MM/[IN].)






**Circuit Diagram** 

Note: The load resistor values should be such that the output current does not exceed the maximum load current of 40 mA.

Use Ohm's Law to calculate the load resistor based on the supply/load voltage used:

R = V / 0.04 A



DEUTSCH DTM04-4P PINOUT (MATING CONNECTOR IS DEUTSCH DTM06-4S)				
Pin 1	Pin 2	Pin 3	Pin 4	
Vsupply	Channel B	Channel A	Ground	

## **⚠ WARNING**PERSONAL INJURY

DO NOT USE these products as safety or emergency stop devices or in any other application where failure of the product could result in personal injury.

Failure to comply with these instructions could result in death or serious injury.

# **⚠ WARNING**MISUSE OF DOCUMENTATION

- The information presented in this product sheet is for reference only.
   Do not use this document as a product installation guide.
- Complete installation, operation, and maintenance information is provided in the instructions supplied with each product.

Failure to comply with these instructions could result in death or serious injury.

### FOR MORE INFORMATION

Honeywell Advanced Sensing
Technologies services its customers
through a worldwide network of sales
offices and distributors. For application
assistance, current specifications, pricing
or the nearest Authorized Distributor,
visit our website or call:

USA/Canada +1 302 613 4491 Latin America +1 305 805 8188 Europe +44 1344 238258 Japan +81 (0) 3-6730-7152 Singapore +65 6355 2828

+86 4006396841

#### WARRANTY/REMEDY

Honeywell warrants goods of its manufacture as being free of defective materials and faulty workmanship during the applicable warranty period. Honeywell's standard product warranty applies unless agreed to otherwise by Honeywell in writing; please refer to your order acknowledgment or consult your local sales office for specific warranty details. If warranted goods are returned to Honeywell during the period of coverage, Honeywell will repair or replace, at its option, without charge those items that Honeywell, in its sole discretion, finds defective. The foregoing is buyer's sole remedy and is in lieu of all other warranties, expressed or implied, including those of merchantability and fitness for a particular purpose. In no event shall Honeywell be liable for consequential, special, or indirect damages.

While Honeywell may provide application assistance personally, through our literature and the Honeywell web site, it is buyer's sole responsibility to determine the suitability of the product in the application.

Specifications may change without notice. The information we supply is believed to be accurate and reliable as of this writing. However, Honeywell assumes no responsibility for its use.

## Honeywell Advanced Sensing Technologies

830 East Arapaho Road Richardson, TX 75081 sps.honeywell.com/ast

Greater China

