

PWS 7032

AIR/WATER HEAT EXCHANGER 300 W

PWS: for outer mounting on the door or side

- robust steel cover, easily paintable
- maintenance-free
- mounting-friendly seal, no elaborate reworking of the mounting cut-out




PRODUCT		PWS 7032	
ARTICLE NO.	Basic	12050380055	Unit
DATA			
Rated voltage $\pm 10\%$		DC	
		24	V
Cooling capacity @ 200 l/h	W10/A35	300	W
Unimpeded airflow (free flow)	internal	80	m ³ /h
Type of connection	electro	spring-type terminal included with plug	
	fluid	13 mm hose nozzle	
Noise level according to EN ISO 3741		63	dB (A)
Weight (without packaging)		5	kg
Ambient temperature range		+1 ... +70 +34 ... +158	°C °F
Water inlet temperature		+1 ... +35 +34 ... +95	
Permissible operating pressure		max. 10	bar
Condensate management		condensate drain	
Protection system according to EN 60529	IP 55	towards the electrical enclosure if used as intended by the manufacturer	
Design	housing	galv. steel electrostatically powder coated (200 °C)	
	heat exchanger	copper pipe with aluminium fins	
Colour	cover	RAL 7035	



Cooling capacity performance curves


Cooling capacity
 Q_0 [W]

Electrical enclosure
internal temperature T_i



Pressure loss performance curves

Pressure loss
[Bar]



Dimensions

	X	Y	Z
mm	150	300	93

PWS 7032

