

Article No. : 6SL4112-0KP20-0FF0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input

Number of phases	3 AC	
Line voltage	200...240V (-20+10 %)	
Line frequency	50/60 Hz (47 ... 63 Hz)	
Voltage range (voltage class)	200 ... 240 V (230V IEC)	200 ... 240 V (240V NEC)
Rated current	66.0 A	62.0 A

Output

Number of phases	3 AC	
Voltage range (voltage class)	200 ... 240 V (230V IEC)	200 ... 240 V (240V NEC)
Rated power (LO)	18.50 kW	25.00 hp
Rated power (HO)	15.00 kW	20.00 hp
Rated current (LO)	75.0 A	68.0 A
Rated current (HO)	63.0 A	54.0 A
Rated current (IN)	77.0 A	69.8 A
Max. output current	126.0 A	
Pulse frequency (factory setting)	4 kHz	
Output frequency for vector control	0 ... 480 Hz	
Output frequency for V/f control	0 ... 550 Hz	

Overload capability

Low Overload (LO)
150% rated current (LO) for 3 s, followed by 110% rated current (LO) for 57 s in a 300 s cycle time
High Overload (HO)
200% rated current (HO) for 3 s, followed by 150% rated current (HO) for 57 s in a 300 s cycle time

Electronic power supply

Voltage	24 V (20.4 ... 28.8 V)
Current demand, max.	2.00 A

General tech. specifications

Power factor λ (typical)	
Displacement factor $\cos \phi$ (typical)	0.98
Efficiency η	0.96
Sound pressure level (1m)	70 dB
Filter class (integrated)	Unfiltered

Communication

Communication PROFINET, Modbus TCP, EtherNet/IP

SINAMICS SDI Standard Operator Panel

User interface

Operator element version	Integrated SDI standard for monitoring and diagnostics
Interface design	RJ45 with 100 MBit/s Ethernet
Display design	1.4" graphic display
Screen resolution	128 x 160 Pixel

Inputs / outputs

Standard digital inputs

Number	6 (additionally 2 AI configurable as 2 DI)
Switching level: 0 → 1	11 V
Switching level: 1 → 0	5 V
Max. inrush current	4 mA
Number as rapid input	1 (DI5)

Fail-safe digital inputs

Number	1 (additionally 4 DI configurable as 2 FDI)
--------	---------------------------------------------

Digital outputs

Number as relay changeover contact	2
Output (resistive load)	DC 30 V, max. 0.5 A
Number as transistor	1
Output (resistive load)	DC 30 V, max. 0.4 A

Analog inputs

Number	2 (Differential input)
Resolution	16 bit

Operating mode

Voltage bipolar	-10 ... 10 V
Voltage unipolar	0 ... 10 V
Current	0 ... 20 mA
Current monitored	4 ... 20 mA

Switching threshold as digital input

0 → 1	11 V
1 → 0	5 V

Data sheet for SINAMICS G220

Article No. : 6SL4112-0KP20-0FF0

Analog outputs

Number	1 (Non-isolated output)
Operating mode	
Voltage unipolar	0 ... 10 V
Current	0 ... 20 mA
Current monitored	4 ... 20 mA

Motor temperature interface

1 input for motor temperature, connectable PTC, KTY 84, PT1000, and bimetal temperature switch

PTC interface

CU: short-circuit monitoring < 20 ohms, overtemperature > 1650 ohms, OM-SMT: type A, in accordance with IEC 60947-8, in accordance with EN 50495

KTY84 interface

Short-circuit monitoring < 500ohm; wire breakage>21200hm; measurement current 2mA

PTC1000 interface

Short-circuit monitoring < 6030hm; wire breakage>21200hm; measurement current 2mA

Closed-loop control techniques

V/f linear / square-law / parameterizable Yes

V/f with flux current control (FCC) Yes

V/f ECO linear / square-law Yes

Sensorless vector control Yes

Vector control, with sensor Yes

Encoderless torque control Yes

Torque control, with encoder Yes

Ambient conditions

Cooling Air cooling using an integrated fan

Cooling air requirement 0.058 m³/s (2.048 ft³/s)

Installation altitude (without derating) 1,000 m (3,281 ft)

Max. ambient temperature with derating 50 °C

Ambient temperature with high overload (without derating) 45 °C

Ambient temperature with low overload (without derating) 40 °C

Relative humidity during

Max. operation 95 %

Environmental conditions

Chemically active substances

Operation Class 3C3, according to IEC 60721-3-3: 2002

Transport Class 2C2 according to IEC 60721-3-2:1997 in marine- and weather-resistant transport packaging

Storage Class 1C2 according to IEC 60721-3-1: 2002 in the transport packaging

Biologically active substances

Operation Class 3B1 according to IEC 60721-3-3: 2002

Transport Class 2B1 according to IEC 60721-3-2:1997 in the transport packaging

Storage Class 1B1 according to IEC 60721-3-1:1997 in the transport packaging

Mechanically active substances

Operation Class 3S2 according to IEC 60721-3-3: Ed. 2.2 2002 (Conductive dusts are not permitted.)

Climatic environmental conditions

Operation Class 3K3 according to IEC 60721-3-3 Ed. 2.2: 2002

Transport Class 2K4 according to IEC 60721-3-2:1997 in the transport packaging; temperature -40 ... +70 °C; relative atmospheric humidity 5..95% (without condensation)

Storage Class 1K4 according to IEC 60721-3-1:1997 in the transport packaging; temperature -25 ... +55 °C; relative atmospheric humidity 5..95% (without condensation), storage altitude <=4000m; condensation, spray water, ice formation, salt mist not permissible

Mechanical environmental conditions

Operation Class 3M1 according to IEC 60721-3-3 Ed. 2.2: 2002

Transport Class 2M3 according to IEC 60721-3-2:1997 in the transport packaging

Storage Class 1M2 according to IEC 60721-3-1:1997 in the transport packaging

Integrated Safety functions

Safety function "Safe Torque Off" Yes

Safe Stop 1 (SS1) Yes

Safe Motor Temperature (SMT) Yes

Extended software functions can be enabled with a license using an SD card.

Data sheet for SINAMICS G220

Article No. : 6SL4112-0KP20-0FF0

Connections

Signal cable

Type	Push-in connection
Conductor cross-section	0.20 ... 2.50 mm ² (24 ... 12 AWG)

Line side

Type	screw terminal
------	----------------

Conductor cross-section

for single-core cables	16.00 ... 50.00 mm ² (6 ... 1/0 AWG)
for multi-core cables	16.00 ... 50.00 mm ² (6 ... 1/0 AWG)

Motor end

Type	screw terminal
Conductor cross-section	10.00 ... 50.00 mm ² (8 ... 1/0 AWG)

DC link

Type	screw terminal
Conductor cross-section	10.00 ... 50.00 mm ² (8 ... 1/0 AWG)

PE connection

Type	M8, screw terminal
Conductor cross-section	10.00 ... 50.00 mm ² (8 ... 1/0 AWG)
Type	stud terminal, M6
Conductor cross-section	10.00 ... 50.00 mm ² (8 ... 1/0 AWG)

Max. motor cable length

Shielded	200 m (656 ft)
Unshielded	300 m (984 ft)

Mechanical data

Degree of protection	IP55 / UL type 12
Frame size	FSD2
Net weight	34.1 kg (75.18 lb)

Dimensions

Width	270 mm (10.63 in)
Height	650 mm (25.59 in)
Depth	283 mm (11.14 in)

Memory card

1 slot for SD card	SINAMICS SD card, 8GByte
--------------------	--------------------------

Certificates

Certificate of suitability	CE, cULus (UL 61800-5-1, CSA 22.2 No. 274), EAC, UKCA
----------------------------	-------------------------------------------------------

CE marking

EMC directive 2014/30/EU; Low Voltage Directive 2014/35/EU; RoHS Directive 2011/65/EU; energy efficiency and eco design 2009/125/EU

Verification of suitability for fail-safety	SIL 3 according to IEC 61508 and IEC 61800-5-2, PL e according to ISO 13849-1, Category 4 according to ISO 13849-1
---------------------------------------------	--------------------------------------------------------------------------------------------------------------------

Environmental compatibility	RoHS II, REACH, Green Passport
-----------------------------	--------------------------------

Explosion protection	according to ATEX Directive 2014/34/EU
----------------------	----------------------------------------


shipbuilding approval	No
-----------------------	----

Converter losses to IEC61800-9-2*

Efficiency class	IE2
In scope of Ecodesign Directive	No (in the valid range)
Reason of exception	no exception

IEC power loss data based on

Input	3 AC 230 V, 50 Hz
Output	3 AC 0 - 230 V, 50 Hz, 4 kHz Space-vector modulation
Rated apparent power	30.7 kVA
Power loss in standby	38.4 W (0.1%)



Data sheet for SINAMICS G220

Article No. : 6SL4112-0KP20-0FF0

NEC power loss data based on


Input	3 AC 240 V, 60 Hz
Output	3 AC 0 - 240 V, 60 Hz, 4 kHz Space-vector modulation
Rated apparent power	29 kVA
Power loss in standby	38.4 W (0.1%)

the absolute power losses for motor voltages according to NEC (AC 230 V, AC 460 V, AC 575 V) are approximately 2 % lower

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values



Data sheet for SINAMICS G220

Article No. : 6SL4112-0KP20-0FF0

Data sheet for Option Module OM-SMT (Safe Motor Temperature)

Electrical data

Operating voltage (DC)	24.0 V (20.4 ... 28.8 V) from internal 24 V supply
Current demand, max.	0.15 A
Power loss	2.4 W

Inputs / outputs

PTC interface

Type A, according to IEC 60947-8; short-circuit detection <10 Ohm; no short-circuit >20 Ohm; overtemperature >2100 Ohm; no overtemperature <1100 Ohm; measuring current 1.5 mA; 1x PTC warning; 1x PTC shutdown (safety).

Mechanical data

Degree of protection	IP20 / UL open type
Net weight	81.6 g (2.88 oz)

Dimensions

Width	65.2 mm (2.57 in)
Height	67.4 mm (2.65 in)
Depth	53.6 mm (2.11 in)

Ambient conditions

Ambient temperature during

Operation	-20 ... 60 °C (-4 ... 140 °F)
Transport	-40 ... 70 °C (-40 ... 158 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

Relative humidity

without condensation	95 %
----------------------	------

Connections

Signal cable

Version	Push-in connection
Conductor cross-section	0.5 ... 2.5 mm ²

Certificates

Certificate of suitability	CU, cULus (UL 61800-5-1, CSA 22.2 No. 274), EAC, RoHS II, REACH, safety according to EC 61800-5-2 and ISO 13849-1, Green Passport
Explosion protection	according to ATEX Directive 2014/34/EU