

Products → Low Voltage Products and Systems → Surge Protective Devices → IEC/EN standard → Furse ESP specific systems protection

Products → Low Voltage Products and Systems → Surge Protective Devices → IEC/EN standard → Furse special products

## General Information

<b>Extended Product Type:</b>	ESP CATV/F
<b>Product ID:</b>	7TCA085400R0122
<b>EAN:</b>	5414363086390
<b>Catalog Description:</b>	ESP CATV/F Surge Protective Device
<b>Long Description:</b>	ESP CATV/F DATA SPD FOR CABLE TV 5-860MHZ WITH F TYPE CONNECTOR

## Additional Information

<b>Ambient Air Temperature:</b>	Operation -40 ... +80 °C
<b>Connection Type:</b>	Screw clamp
<b>Country of Origin:</b>	United Kingdom (GB)
<b>Customs Tariff Number:</b>	8536308000
<b>Data Sheet, Technical Information:</b>	9AKK10103A0362
<b>Declaration of Conformity - CE:</b>	9AKK106713A1078
<b>EAN:</b>	5414363086390
<b>ETIM 4:</b>	EC000943 - Surge protection device for data networks/MCR-technology
<b>ETIM 5:</b>	EC000943 - Surge protection device for data networks/MCR-technology
<b>ETIM 6:</b>	EC000943 - Surge protection device for data networks/MCR-technology
<b>Instructions and Manuals:</b>	9AKK106713A1369
<b>Invoice Description:</b>	ESP CATV/F Surge Protective Device
<b>Maximum Continuous Operating Voltage (U<sub>c</sub>):</b>	140 V
<b>Minimum Order Quantity:</b>	1 piece
<b>Nominal AC Voltage of the System (U<sub>0</sub>):</b>	140 V
<b>Package Level 1 EAN:</b>	5414363086390
<b>Package Level 1 Units:</b>	1 piece
<b>Product Main Type:</b>	Data SPD
<b>Product Name:</b>	Surge Protective Device
<b>Product Net Depth:</b>	23 mm
<b>Product Net Height:</b>	58 mm
<b>Product Net Weight:</b>	0.14 kg
<b>Product Net Width:</b>	75 mm
<b>Rated Current (I<sub>n</sub>):</b>	4 A
<b>Rated Frequency (f):</b>	50 / 60 Hz
<b>Selling Unit of Measure:</b>	piece
<b>Serial Resistance:</b>	75 Ω
<b>Short Description:</b>	ESP CATV/F
<b>Standards:</b>	IEC 61643-21
<b>Suitable For:</b>	To protect systems against transient overvoltages or surges from lightning and electrical switching events
<b>Voltage Protection Level (U<sub>p</sub>):</b>	245 V

