



Connectors > Automotive Connectors > Connector Accessories > Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover - Cable Exit**

Cable Exit Angle: **90° (Right Angle)**

Strain Relief: **Without**

Primary Product Color: **Black**

Primary Product Material: **PA GF**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover - Cable Exit
Connector System	Wire-to-Board, Wire-to-Device

Configuration Features

Number of Positions	25
---------------------	----

Body Features

Cable Exit Angle	90° (Right Angle)
Primary Product Color	Black
Primary Product Material	PA GF

Mechanical Attachment

Strain Relief	Without
---------------	---------

Dimensions

Cable Bundle Diameter	26 mm[1.024 in]
-----------------------	-----------------

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F]
-----------------------------	---



	°F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F]
--	---

Operating Temperature Range -40 – 140 °C[-40 - 284 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box
Packaging Quantity	300

Other

Serviceable	Yes
-------------	-----

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Model / Part # CAT-L489-CH8172
LEAVYSEAL HOUSINGS



TE Model / Part # 1-2328352-2
25POS, MIXED,REC HSG,ASSY,
SEALED, COD A

Customers Also Bought



TE Model / Part #2-1377173-0
SMP 0-0034156-0



TE Model / Part #9-1377172-4
SMP 0-0034142-0



TE Model / Part #2150529-2
OCEAN_2.0_APPLICATOR-E-
091F130FA



TE Model / Part #2837326-2
OCEAN_2.0_APPLICATOR-S-
216F272OVA



TE Model / Part #2837691-2
OCEAN-2.0-APPLICATOR-S-118F158O



TE Model / Part #4-1377174-5
SMP 1-0160304-2



TE Model / Part #7-2151381-7
OC-106F160O-CRIMPTOOLINGKIT



TE Model / Part #7-2836144-7
OC-092F-CRIMPTOOLINGKIT



TE Model / Part #CH45006001
QSZH-125-NR1-45MM



TE Model / Part #
ANVIL, WIRE

Documents

Product Drawings
COVER,90,25/29POS REC HSG
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2327810-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2327810-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2327810-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Product Specifications](#)

[Application Specification](#)

English