

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

FO connectors, degree of protection: IP20, number of positions: 2, MM, material: Metal, connection method: Push-pull, cable outlet: straight



Product description

SC-RJ fiber optic connector, IP20, duplex, with fast connection technology, for polymer fiber 980/1000 µm, for individual wire diameter 2.2 mm

Your advantages

- Compact design, thanks to SC-RJ pin connector pattern
- Outstanding transmission properties
- Suitable for quick and easy field assembly or repair
- No bonding or polishing
- Flexible application, thanks to reusable connector

Commercial data

Item number	2708656
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABNIAA
Product key	ABNIAA
Catalog page	Page 379 (C-8-2015)
GTIN	4046356123327
Weight per piece (including packing)	37.42 g
Weight per piece (excluding packing)	19.4 g
Customs tariff number	85367000
Country of origin	DE

## Technical data

### Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 8.3 Connectors for inside environment (optical fibre)
---------	--

### Product properties

Product type	Data connector (cable side)
Application	neutral
Type	SC-RJ
Number of positions	2
Connection profile	SC-RJ
Type	SC-RJ
Cable outlet	straight

### Data management status

Article revision	04
------------------	----

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Attenuation	< 1.5 dB (Insertion attenuation)
Transmission medium	FO
Transmission characteristics (category)	MM

### Connection data

#### Connection technology

Connection method	Push-Pull
-------------------	-----------

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	nickel-plated

### Cable/line

Cable type	Plastic fiber
External cable diameter	2.2 mm ... 2.2 mm

#### FO cable

Number of fibers	2
Fiber	POF, PCF, GOF
Fiber type	GOF, PCF, POF

# PSM-SET-SCRJ-DUP/2-POF - FO connectors



2708656

<https://www.phoenixcontact.com/gb/products/2708656>

Transmission medium	FO
---------------------	----

## Characteristics

Attenuation	< 1.5 dB (Insertion attenuation)
-------------	----------------------------------


## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C

## Drawings

Schematic diagram



# PSM-SET-SCRJ-DUP/2-POF - FO connectors



2708656

<https://www.phoenixcontact.com/gb/products/2708656>

## Classifications

### ECLASS

ECLASS-11.0	19170122
ECLASS-12.0	19170122
ECLASS-13.0	19170122

### ETIM

ETIM 9.0	EC001122
----------	----------

### UNSPSC

UNSPSC 21.0	43223300
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%