

Article No. : 6SL4113-2CA17-2AF0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Figure similar



Rated data

Input		
Number of phases	3 AC	
Line voltage	380...415V / 440...500V (–20+10 %)	
Line frequency	50/60 Hz (47 ... 63 Hz)	
Voltage range (voltage class)	380 ... 415 V (400V IEC)	440 ... 500 V (480V NEC)
Rated current	20.6 A	17.5 A

Output		
Number of phases	3 AC	
Voltage range (voltage class)	380 ... 415 V (400V IEC)	440 ... 500 V (480V NEC)
Rated power (LO)	11.00 kW	15.00 hp
Rated power (HO)	7.50 kW	10.00 hp
Rated current (LO)	27.0 A	21.0 A
Rated current (HO)	19.0 A	14.0 A
Rated current (IN)	27.7 A	21.6 A
Rated Current (SRM)	27.0 A	
Max. output current	40.5 A	
Pulse frequency (factory setting)	4 kHz	
Output frequency for vector control	0 ... 480 Hz	
Output frequency for V/f control	0 ... 550 Hz	

Overload capability	
Low Overload (LO)	
150% rated current (HO) for 3 s, followed by 110% rated current (HO) for 57 s in a 300 s cycle time	
High Overload (HO)	
200% rated current (HO) for 3 s, followed by 150% rated current (HO) for 57 s in a 300 s cycle time	

Electronic power supply	
Voltage	24 V (20.4 ... 28.8 V)
Current demand, max.	2.00 A

General tech. specifications	
Power factor λ (typical)	1.00
Displacement factor cos φ (typical)	0.98
Efficiency η	0.97
Sound pressure level (1m)	70 dB
Filter class (integrated)	RFI suppression filter for Category C2

Communication	
Communication	PROFINET, Modbus TCP, EtherNet/IP

SINAMICS SDI Standard Operator Panel

User interface	
Operator element version	Integrated SDI standard for monitoring and diagnostics
Interface design	RJ45 with 100 MBit/s Ethernet
Display design	1.4" graphic display
Screen resolution	128 x 160 Pixel

Inputs / outputs

Standard digital inputs	
Number	6 (additionally 2 AI configurable as 2 DI)
Switching level: 0 → 1	11 V
Switching level: 1 → 0	5 V
Max. inrush current	4 mA
Number as rapid input	1 (DI5)

Fail-safe digital inputs	
Number	1 (additionally 4 DI configurable as 2 FDI)

Digital outputs	
Number as relay changeover contact	2
Output (resistive load)	DC 30 V, max. 0.5 A
Number as transistor	1
Output (resistive load)	DC 30 V, max. 0.4 A

Analog inputs	
Number	2 (Differential input)
Resolution	16 bit

Operating mode	
Voltage bipolar	–10 ... 10 V
Voltage unipolar	0 ... 10 V
Current	0 ... 20 mA
Current monitored	4 ... 20 mA

Switching threshold as digital input	
0 → 1	11 V
1 → 0	5 V

Data sheet for SINAMICS G220 Clean Power

Article No. : 6SL4113-2CA17-2AF0

Analog outputs

Number	1 (Non-isolated output)
Operating mode	
Voltage unipolar	0 ... 10 V
Current	0 ... 20 mA
Current monitored	4 ... 20 mA

Motor temperature interface

1 input for motor temperature, connectable PTC, KTY 84, PT1000, and bimetal temperature switch
--

PTC interface

Short-circuit monitoring < 200Ohm, overtemperature>1650Ohm
--

KTY84 interface

Short-circuit monitoring < 500Ohm; wire breakage>2120Ohm; measurement current 2mA

PTC1000 interface

Short-circuit monitoring < 603Ohm; wire breakage>2120Ohm; measurement current 2mA

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	Yes
Encoderless torque control	Yes
Torque control, with encoder	Yes

Ambient conditions	
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.039 m³/s (1.377 ft³/s)
Installation altitude (without derating)	1,000 m (3,281.00 ft)
Max. ambient temperature with derating	60 °C
Ambient temperature with high overload (without derating)	50 °C
Ambient temperature with low overload (without derating)	45 °C

Relative humidity during

Max. operation	95 %
----------------	------

Environmental conditions	
Chemically active substances	
Operation	Class 3C2, according to IEC 60721-3-3: 2002
Transport	Class 2C2 according to IEC 60721-3-2:1997 in marine- and weather-resistant transport packaging
Storage	Class 1C2 according to IEC 60721-3-1: 2002 in the transport packaging
Biologically active substances	
Operation	Class 3B1 according to IEC 60721-3-3: 2002
Transport	Class 2B1 according to IEC 60721-3-2:1997 in the transport packaging
Storage	Class 1B1 according to IEC 60721-3-1:1997 in the transport packaging
Mechanically active substances	
Operation	Class 3S1 according to IEC 60721-3-3: Ed. 2.2 2002 (Conductive dusts are not permitted.)
Climatic environmental conditions	
Operation	Class 3K3 according to IEC 60721-3-3 Ed. 2.2: 2002
Transport	Class 2K4 according to IEC 60721-3-2:1997 in the transport packaging; temperature -40 ... +70 °C; relative atmospheric humidity 5..95% (without condensation)
Storage	Class 1K4 according to IEC 60721-3-1:1997 in the transport packaging; temperature -25 ... +55 °C; relative atmospheric humidity 5..95% (without condensation), storage altitude <=4000m; condensation, spray water, ice formation, salt mist not permissible
Mechanical environmental conditions	
Operation	Class 3M1 according to IEC 60721-3-3 Ed. 2.2: 2002
Transport	Class 2M3 according to IEC 60721-3-2:1997 in the transport packaging
Storage	Class 1M2 according to IEC 60721-3-1:1997 in the transport packaging
Integrated Safety functions	
Safety function "Safe Torque Off"	Yes
Safe Stop 1 (SS1)	Yes
Safe Motor Temperature (SMT)	No
Extended software functions can be enabled with a license using an SD card.	

Data sheet for SINAMICS G220 Clean Power

Article No. : 6SL4113-2CA17-2AF0

Connections	
Signal cable	
Type	Push-in connection
Conductor cross-section	0.20 ... 2.50 mm² (24 ... 12 AWG)
Line side	
Type	screw terminal
Conductor cross-section	
for single-core cables	6.00 ... 35.00 mm² (10 ... 2 AWG)
for multi-core cables	6.00 ... 35.00 mm² (10 ... 2 AWG)
Motor end	
Type	screw terminal
Conductor cross-section	6.00 ... 35.00 mm² (10 ... 2 AWG)
DC link	
Type	screw terminal
Conductor cross-section	6.00 ... 35.00 mm² (10 ... 2 AWG)
PE connection	
Type	M5, screw terminal
Conductor cross-section	6.00 ... 35.00 mm² (10 ... 2 AWG)
Max. motor cable length	
Shielded	200 m (656.17 ft)
Unshielded	300 m (984.25 ft)
with EMC category C2	
Shielded	150 m (492.13 ft)


Mechanical data	
Degree of protection	IP20 / UL open type
Frame size	FSD1
Net weight	16.9 kg (37.26 lb)
Dimensions	
Width	150 mm (5.91 in)
Height	400 mm (15.75 in)
Depth	245 mm (9.65 in)

Memory card	
1 slot for SD card	SINAMICS SD card, 8GByte

Certificates	
Certificate of suitability	CE, KC, cULus (UL 61800-5-1, CSA 22.2 No. 274) , EAC, UKCA
CE marking	
EMC directive 2014/30/EU; Low Voltage Directive 2014/35/EU; RoHS Directive 2011/65/EU; energy efficiency and eco design 2009/125/EU	
Verification of suitability for fail-safety	SIL 3 according to IEC 61508 and IEC 61800-5-2, PL e according to ISO 13849-1, Category 4 according to ISO 13849-1
Environmental compatibility	RoHS II, REACH, Green Passport
Explosion protection	-
shipbuilding approval	No

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
In scope of Ecodesign Directive	No (Not in the scope of the ecodesign guideline)
Reason of exception	sinusoidal input current

IEC power loss data based on	
Input	3 AC 400 V, 50 Hz
Output	3 AC 0 - 400 V, 50 Hz, 4 kHz Space-vector modulation
Rated apparent power	19.2 kVA
Power loss in standby	32.2 W (0.2%)



Data sheet for SINAMICS G220 Clean Power

Article No. : 6SL4113-2CA17-2AF0

NEC power loss data based on

Input	3 AC 480 V, 60 Hz
Output	3 AC 0 - 480 V, 60 Hz, 4 kHz Space-vector modulation
Rated apparent power	18 kVA
Power loss in standby	32.2 W (0.2%)

the absolute power losses for motor voltages according to NEC (AC 230 V, AC 460 V, AC 575 V) are approximately 2 % lower

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

