




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Termination Method to Wire & Cable: **Crimp**
Connector System: **Wire-to-Panel, Wire-to-Wire**
Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Yellow
-----------------------	--------

Contact Features

--	--



Multiple Contact Types	Without
Contact Layout	Inline
Contact Type	Pin
Contact Retention Within Housing	Without

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Patch & Tabs
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Nylon
Centerline (Pitch)	6.35 mm[.25 in]

Dimensions

Panel Thickness (Recommended)	.76 – 2.29 mm[.03 – .09 in]
-------------------------------	-----------------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 926900-3
UNIV-MNL STIFT



TE Part # 926901-3
UNIV-MNL BUCHSE



TE Part # 350550-6
UMNL SOK 20-14 AU/PHBZ L/P



TE Part # 350700-2
UMNL SPLIT PIN AU/NI/BR



TE Part # 926895-1
UNIVERSAL M-N-L SOCKET



TE Part # 926885-1
UNIV.M-N-L.PIN



TE Part # 926895-3
UNIVERSAL M-N-L SOCKET



TE Part # 926886-1
UNIV.M-N-L.PIN





TE Part # 926895-7
UNIVERSAL M-N-L SOCKET



TE Part # 926894-1
UNIV.M-N-L.PIN




TE Part # 926868-1
UNIV.M-N-L.PIN



TE Part # 926898-1
UNIV.M-N-L.PIN




TE Part # 1586076-1
02P UMNL PIN HDR W/O DRNS V2




TE Part # 350218-2
UMNL PIN 20-14 .0126AUBR



TE Part # 350551-3
UMNL SOK 20-14 PTPPHBZ L/P



TE Part # 350923-4
UMNL SOK 12-10 AUPHBZ



TE Part # 350687-2
UMNL SPLIT PIN AUBR



TE Part # 350689-2
UMNL SOK 24-18 AUBR L/P



TE Part # 350690-1
UMNL PIN 24-18 PTPBR L/P



TE Part # 350561-2
UMNL PIN 24-18 .0126 AU/BR

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Contacts(208)



Connector Hardware(12)



Power Contacts(208)



Rectangular Power Connectors(651)



Standard Circular Connectors(1)

Customers Also Bought



TE Part #1-480700-2
03P UMNL PLUG HSG RED



TE Part #1-480701-8
03P UMNL CAP HSG GRY



TE Part #1-480702-9
04P UMNL PLUG HSG BLK



TE Part #1-480703-2
04P UMNL CAP HSG RED



TE Part #41481
250 FASTON TAB TPBR



TE Part #1-480701-9
03P UMNL CAP HSG BLK



TE Part #350538-1
UMNL PIN 20-14 .0126 PTPBR



TE Part #1-480703-9
04P UMNL CAP HSG BLK



TE Part #1-480703-1
04P UMNL CAP HSG BRN



TE Part #1-480701-2
03P UMNL CAP HSG RED

Documents

Product Drawings
04P UMNL CAP HSG YELL

English

CAD Files
Customer View Model
ENG_CVM_CVM_1-480703-4_BP1.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1-480703-4_BP1.2d_dxf.zip

English

3D PDF

3D
Customer View Model
ENG_CVM_CVM_1-480703-4_BP1.3d_stp.zip

English

Datasheets & Catalog Pages



SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English