

8572-01

Torque wrench DREMOMETER

1500-3000 Nm

Code **7717160** ETIM **EC002132**

EAN **4002805857212** UNSPSC **27-11-17-15**

Country of origin **Germany** eCI@ss **21-04-02-22**

Customs tariff number
82041100



Article description

- Use:
Controlled screw tightening in the range of 1500 - 3000 Nm
- For use in almost all industrial manufacturing areas
- Features:
Classified according to DIN EN ISO 6789-2:2017 Type II Class A, incl. traceable test certificate, calibrated to a maximum permissible deviation of +/- 3 % and thus more precise than the +/- 4 % required by the standard
1.1/2" square drive with pin-locking mechanism DIN 3121 - F 40, ISO 1174
Automatic short-path actuation with tactile impulse and audible signal
Single scale with a scale graduation of 50 Nm
- Technical advantage/Function:
Lightweight yet robust (as the housing is made of an aluminium alloy) and resilient, very workshop-friendly
No inaccuracies whether used with both hands or held away from the handle (as for standard torque wrenches)
Both the square drive and fulcrum are on an axis which ensures a high degree of user safety; can be extended to reduce the user's working load.
Extremely low wear attributable to reduced forces in a lever mechanism
Forged lever chain from our group own quality forge
Maximum precision even when subjected to extreme continuous use
Long life cycles and tool lives
Easy operation - fast and safe torque tightening
Easy adjustment thanks to attractive adjusting button secured against loss at the end of the handle
For controlled clockwise tightening

Article parts list

Extension tube,8564-92,8572-74

Article information

Contents [Qty of pieces]	1	Trigger mechanism	Short path triggering
Net weight [kg]	15 kg	Precision +/-	+/- 3 %
Total length [mm]	1.037 mm	Direction of tightening	Right
Total width [mm]	70 mm	Fixed setting	no
Total height [mm]	40 mm	Test certificate	DIN EN ISO 6789-2:2017
Material	Aluminum alloy	Head height 1 [mm]	40 mm
Standard	ISO 1174 DIN 3121 - F40	Width of head 1 [mm]	70,0 mm
Drive connector square (male)	1.1/2"	Torque wrench type	F
Drive connector square (male)	40 mm	Calibration length	2309 mm
Drive type/drive	Single square	Distance housing - square drive	35 mm
Torque (min.) [Nm]	1500 Nm	Storage/Content	Box
Torque (max.) [Nm]	3000 Nm	Length of extension tube 1	925 mm
Torque range (min./max.) [Nm]	1500 Nm - 3000 Nm	Length of slip-on tube 2	745 mm
Torque range (min./max.) [lbf·ft]	-		