



**Part Number :** [445600024](#)

**Product Description :** Modular Jack, Right-Angle, Low Profile, Shielded, 8/8, 4 Ports



**Series Number :** 44560

**Status :** Active

**Product Category :** Modular Jacks and Plugs

## Documents & Resources

### Drawings

[445600024\\_sd.pdf](#)

[PK-44560-005-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-44560-003-001.pdf](#)

[TS-44560-003-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Modular Jacks and Plugs
Series	44560
Description	Modular Jack, Right-Angle, Low Profile, Shielded, 8/8, 4 Ports
Comments	Bezel Shield
Component Type	PCB Jack
Magnetic	No
Performance Category	5, 5e
Power over Ethernet (PoE)	N/A
Product Name	Modular Jack 8/8,RJ45
UPC	756054374412

#### Agency

CSA	LR19980
UL	E107635

#### Electrical

Current - Maximum per Contact	1.5A
Shielded	Yes
Voltage - Maximum	150V

## Physical

Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Inverted / Top Latch	No
Jack Height	11.23mm
Lightpipes/LEDs	None
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	12.057/g
Orientation	Right Angle (Side Entry)
Packaging Type	Tray
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.02mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	1.270µm
Plating min - Termination	2.540µm
Port Configuration	1x4
Positions / Loaded Contacts	8/8
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole
Wire/Cable Type	N/A

## Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	260

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Mates With	FCC 68 Plugs

---

This document was generated on Aug 06, 2025