




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **6**
Terminal Orientation: **Straight**
Primary Product Color: **Black**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	6
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	With
------------------	------



Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Material	Nylon
Centerline (Pitch)	9.04 mm[.356 in]
Dimensions	
Product Length	28 mm[1.1 in]
Usage Conditions	
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
Packaging Features	
Packaging Quantity	700
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2016 (169) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 170349-2 FF 250 TAB 22-20AWG TPBR WITHOUT LATCH	 TE Part # 626213-2 3 CIR FASTIN-ON RECP HSG PRETO	 TE Part # 170349-1 FF 250 TAB 22-20AWG BR WITHOUT LATCH	 TE Part # 1534690-1 FASTIN FASTON HOUSING 4POS 2,8 MM
 TE Part # 880137-2 3W FASTIN-ON REC. HSG	 TE Part # 170340-3 FF 250 TAB 20-14AWG PTBR WITHOUT LATCH	 TE Part # 170258-2 FF 250 REC 14-12AWG TPBR REREELING	 TE Part # 1982859-1 FASTON HOUSING
 TE Part # 880107-2 HOUSING 8P .110 FASTON	 TE Part # 150653-1 FF 312 REC HSG 3P NYLON BLACK	 TE Part # 926728-1 FF 110 REC HSG 4P NYLON BLACK	 TE Part # 170341-3 FF 250 TAB 14-12AWG PTBR WITHOUT LATCH
 TE Part # 170340-1 FF 250 TAB 20-14AWG BR WITHOUT LATCH	 TE Part # 521381-1 FF 187 REC HSG 6P NYLON BLACK	 TE Part # 880103-1 5 WAY FASTIN ON HSG	 TE Part # 170258-1 FF 250 REC 14-12AWG BR REREELING
 TE Part # 480100-1 FF 312 REC HSG 3P NYLON BLACK			

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(195)



Insertion & Extraction Tools(2)




Quick Disconnects(216)

Customers Also Bought




TE Part #1074374005
DWTC-8/2-X-SP



TE Part #6-1879273-4
RP 2A 866R 0.1% 15PPM CUT LENGTH



TE Part #4-2176345-2
CRGCQ 1210 27K 1%



TE Part #1969613-8
8P PM PLUG VAL-U-LOK V0



TE Part #1-2176246-7
CRGS2512 5% 22R



TE Part #213782-1
CPC RECPT ASSEMBLY SIZE 23-19



TE Part #213855-1
CPC RECPT ASSEMBLY SIZE 17-16



TE Part #213798-1
CPC RECPT ASSEMBLY SIZE 23-24



TE Part #1-2176086-8
3654 0402 9nH 5% 2K RL



TE Part #1558665-8
T9GS5L14-48

Documents

Product Drawings

FF 250 REC HSG 6P NYLON BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_140885-5_P_c-140885-5-p.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_140885-5_P_c-140885-5-p.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_140885-5_P_c-140885-5-p.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[White Paper: Nylon Discoloration](#)

English

Product Specifications

[Application Specification](#)

English