

Han 6EMC/B-HBM - w/o SL



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 62 806 0303 |
| Specification | Han 6EMC/B-HBM - w/o SL |
| HARTING eCatalogue | https://harting.com/09628060303 |

Identification

| | |
|-----------------------------|--------------------------|
| Category | Hoods / Housings |
| Series of hoods/housings | Han [®] EMC/B |
| Type of hood/housing | Bulkhead mounted housing |
| Description of hood/housing | Internal seal |
| Type | Low construction |

Version

| | |
|----------------------|--|
| Size | 6 B |
| Locking type | Single locking lever (on the hood) |
| Field of application | Hoods/Housings for higher EMC requirements |

Technical characteristics

| | |
|--|--|
| Tightening torque | 1 Nm Fixing screws M4 |
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Mating cycles | ≥500 |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 12 |

Material properties

| | |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Uncoated |



Pushing Performance
Since 1945

Material properties

| | |
|-----------------------------|---------------|
| Colour (hood/housing) | Unpainted |
| Material (seal) | NBR |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |

Specifications and approvals

| | |
|-----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 80.14 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140171701 |
| eCl@ss | 27440202 Shell for industrial connectors |
| ETIM | EC000437 |
| UNSPSC 24.0 | 39121466 |