

318.3246

CONNECTOR
32A 3P+E 6h 380-415V 60Hz 50Hz
Screw terminals



* Product image may be indicative



EN IEC 60309-1 (2022)
EN IEC 60309-2 (2022)
Low voltage direct. 2014/35/EU

GENERAL CHARACTERISTICS

Commercial Series	OPTIMA Series
Synthetical description	CONNECTOR
Description	
The OPTIMA Series connector is designed for demanding electrical industrial environments, featuring a rated voltage of 380-415V and a rated current of 32A. This connector includes a 3P+E configuration and a 6h hour position, ensuring dependable performance across various applications. It offers a high protection degree of IP66/IP67/IP69, providing exceptional resistance to dust and water ingress. Equipped with screw terminals, it ensures secure and efficient connections. Available in a straight outlet type, this connector is engineered to meet the rigorous demands of industrial settings, ensuring both durability and reliability.	
Mounting version	PORTABLE

TECHNICAL CHARACTERISTICS

Rated current	32A
Poles	3P+E
Hour position	6h
Rated voltage	380-415V
Working frequency	60Hz
	50Hz
Terminals	Screw terminals

PHYSICAL CHARACTERISTICS

Mounting version	PORTABLE
Colour	RED
Material	THERMOPLASTIC
Protection degree	Watertight
Protection degree IP	IP66/IP67/IP69
Protection degree IK	IK08
Types of available outlets	STRAIGHT
Contact material	CuZn (brass)
Cable entry	CABLE GLAND

DOWNLOAD

Technical drawing [PDF]
Technical drawing [STP]
Technical drawing [DWG]