

Article No. : 1FL2204-2AF00-0SC0



Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Basic motor data	
Motor type	Permanent-magnet synchronous motor
Motor type	Medium Inertia
Static torque	2.40 Nm
Static current	2.25 A
Maximum torque	7.50 Nm
Maximum current	7.1 A
Maximum speed	6,500 rpm
Rotor moment of inertia	1.2300 kgcm ²
Weight	2.6 kg

Rated data	
SINAMICS S200, 3 AC 380 ... 480 V	
Rated speed	3,000 rpm
Rated torque	2.40 Nm
Rated current	2.2 A
Rated power	0.75 kW

Encoder system	
Encoder system	Absolute encoder singleturn 21 bit

Motor connection	
Connection type	Metal hybrid connector

Mechanical data	
Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	40
Flange size (AB)	81 mm
Centering ring (N)	70 mm
Hole circle (M)	90 mm
Screw-on hole (S)	6.6 mm
Overall length (LB)	124.6 mm
Diameter of shaft (D)	19 mm
Length of shaft (E)	40 mm
Length of flange diagonal (P)	104.9 mm
Shaft end	Plain shaft
Color of the housing	Anthracite RAL 7016

