



PRO building site range

Identity	PRO building site cable reel
Brand	Schneider Electric
Item number	IMT33130
EAN code	3606480985645

Product Specifications

Length	25 m
Cable quality	H07RN-F 3G1,5mm ²
Cable	TITANEX™
Waterproof quality	IP44
Use	Outdoor
Sockets	4 sockets 2P+T - 16A – 230V protective caps and child safety
Thermal cut-out protection	Automatic interruption of the current in case of cable overheat
Power – extended cable	3600W max
Power – reeled cable	920W
Packaged product dimensions L x W x H	25x33x34cm – weight 5,7Kg
Norm	Complies with NF EN61242 norm

- Câble souple
- Sans plomb
- Température max. sur l'âme: 60°C
- Résistance accident chimique
- Résistance aux chocs
- Étanchéité AD6
- Résistance aux huiles
- Température ambiante d'utilisation: 53°C / -25°C

Advantages of our product

- > TITANEX™ cable : flexible and resistant to impacts
- > Retractable crank handle
- > 3 years guarantee
- > Ergonomic handle

