

product type designation

product description



Distance piece MDS D139

Support for mounting heat-resistant transponders with 30 mm distance to metal
MOBY D spacer for MDS D139.

suitability for use	The support and transponder are mounted using an M5 screw
suitability for operation	for holding the transponders MDS D139/D339
mechanical data	
material	PPS
color	black
ambient conditions	
ambient temperature	
• during operation	-40 ... +220 °C
• during storage	-40 ... +220 °C
• during transport	-40 ... +220 °C
design, dimensions and weights	
height	30 mm
diameter	85 mm
net weight	80 g
further information / internet links	
internet link	
• to website: TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to web page: selection aid TIA Selection Tool	https://support.industry.siemens.com/cs/ww/en/view/67384964
• to the website: IWLAN	http://www.siemens.com/iwlan
• to website: Industrial communication	http://www.siemens.com/ident/rfid
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified: 11/9/2023 