


■ GEBERIT



Example image

APPLICATION PURPOSES

- | APPLICATION PURPOSES | |
|--|--|
| <ul style="list-style-type: none"> • For cold and hot potable water • For cooling and heating water without antifreeze agent • For cooling and heating water with antifreeze agent • For district heating water $\leq 120\text{ }^{\circ}\text{C}$ • For saturated steam $\leq 120\text{ }^{\circ}\text{C}$ • For service water and process water • For treated water • For grey and black water with a pH value ≥ 5.5 | <ul style="list-style-type: none"> • For extinguishing water (wet) • For extinguishing water (wet/dry, dry) • For sprinklers (wet) • For chemicals and technical liquids • For compressed air (oil purity class 0–3) • For negative pressure • For inert gases (e.g. nitrogen) • For industrial gases (e.g. acetylene, shielding gases) • For technical building systems, industry and shipbuilding |

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black

TECHNICAL DATA

Product material	CrNiMo steel 1.4401 (EN 10088)
------------------	--------------------------------

Art. no.	DN	d, ø mm	E cm	L cm	Z cm
82102	12	15	2.5	8	3
82103	15	18	2.5	8	3
82104	20	22	2.5	8.4	3.4
82105	25	28	3	9.1	3.1

Art. no.	DN	d _g mm	E cm	L cm	z cm
82106	32	35	3	10.2	4.2
82107	40	42	4	12	4
82108	50	54	4	14	6
82109	65	76.1	6	23	11
82110	80	88.9	7	26	12
82111	100	108	8	31	15