

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

20

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.
TOUS DROITS RESERVES

FILES ADMISSIBLES (ACCEPTABLES WIRES)

JAUGE (AWG)
SECTION / 7 BRINS (7 STRANDS)

28-26
0.08-0.12mm²

ISOLANT: Ø MAX / MATIERE
(INSUL.: Ø MAX / MAT'L)

Ø 1 / PVC

LOC
F

DIST
7

REVISIONS

P	LTR	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	A	REDESSINE	06/90	AC'	-
	B	REDESSINE SUR (REDRAWN ON) PRO/ENG	10SEP2002	CC	YP
	C	UPDATED	28MAR2007	TC	YP

2.54

DIM A

VOIE N°1
(FIRST POSITION)

17.8±0.2

4

REPERE VOIE N°1
(POSITION NUMBER 1)

"B" ^{+0.12}₀

"C"±0.4

5.1⁰_{-0.3}

8.9 MIN

3.4⁰_{-0.1}

4.5⁰_{-0.1}

1.8±0.2

4.5⁰_{-0.1}

SCALE 4:1

SCALE 4:1

1

2

3

4

5

CES CONNECTEURS SONT PREVUS POUR ETRE
ACCOUPLES AVEC LES EMBASES 'HE1402'
SIMPLE RANGEE

LES REFERENCES SUIVIES D'UN ' * ' SONT
LES VERSIONS NORMALISEES
SELON LA 'CEI 603-8'

REJETEMENT DES CONTACTS: ETAME

8.6 SIGNIFIE JAUGE 28-26

MATIERES - BOITIER: PBT UL94V0, BLEU
- CONTACTS: BRONZE PHOSPHOREUX.

(THESE CONNECTEURS ARE DESIGNED TO BE MATED
WITH 'HE1402' HEADERS SINGLE ROW)
-

(THE PART-NO FOLLOWED BY ' * ' ARE
COVERED BY THE INTERNATIONAL STANDARD 'IEC603-8')

(CONTACTS PLATING: TIN)

8.6 REFERS TO 28-26 AWG

(MATERIAL - HOUSING: PBT UL94V0, COLOR BLUE
- CONTACTS: PHOSPHOR BRONZE)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.
CE PLAN EST UN DOCUMENT CONTRÔLÉ PAR AMP INCORPORATED.
IL EST SUSCEPTIBLE D'ÊTRE RÉVISÉ, CONTACTER LE SERVICE
TECHNIQUE D'AMP DE FRANCE POUR OBTENIR LA DERNIÈRE RÉVISION.

DIMENSIONS:

mm

MATERIAL/MATIERE

5

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
(SUIV NB DE DECIMALES)
0 PLC/DEC: ±
1 PLC/DEC: ±0.3
2 PLC/DEC: ±
3 PLC/DEC: ±
4 PLC/DEC: ±
ANGLES ±°

FINISH/FINITION

3

DWN/DESSINE
C. COMBEDOUZON
CHK/VERIFIE
T. CORRIEU
APVD/APPROUVE
Y. PETRONIN
PRODUCT SPEC
SPEC, PRODUIT
108-15053
APPLICATION SPEC
SPEC, APPLICATION
114-15031
WEIGHT
MASSE APPROX. -
CUSTOMER DRAWING /PLAN CLIENT

29NOV2000
29NOV2000
29NOV2000

AMP DE FRANCE
95301 PONTOISE

HE 1402 PLUG,
180° IDC SINGLE ROW
-

SIZE
FORMAT
A2

CAGE CODE
00779

DRAWING NO
No PLAN
C=281786

RESTRICTED TO
RESERVE A
-

UNIQUEMENT
POUR REFERENCE

SCALE
Echelle 5:1

SHEET
FEUILLE

OF
DE

REV
C

AMP 1471-9 REV 31MAR2000