



HelaTape

HellermannTyton offers a comprehensive range of PVC and rubber tapes for bundling, insulating, fixing, sealing and marking applications around all kinds of electrical applications. PVC-based tapes are designed for low voltage applications and available in a variety of dimensions and colours. Rubber tapes are suitable for sealing and insulating cables and splices in low, medium and very high voltage applications. Cloth tapes are extremely strong and ideal for identification, fixing and repair purposes.

HelaTape Flex - Vinyl Electrical Tapes

HelaTape Flex 15 - All Purpose Vinyl Insulating Tape

Features and Benefits

- Polyvinyl chloride insulating tape in many different colours
- Used for insulation, protection, fixing, maintenance, colour coding and more
- Good resistance to abrasion, moisture, chemicals, and varying weather conditions
- Highly flexible with good adhesion level
- Harnessing of wires and cables
- Suitable for mechanical and electrical applications up to 600 volts
- Meets IEC 60454-3-1-5/F-PVCP/90 requirements
- Flame retardant



Highly flexible and with good adhesion levels HelaTape Flex 15 can be used in several applications.



One Step to the Web!

MATERIAL	Polyvinylchloride (PVC)
Dielectric Strength	40 kV/mm
Adhesion to Steel	2.0 N/10 mm
Adhesion to Backing	1.8 N/10 mm
Elongation at break	200 %
Breaking Strength	24 N/10 mm
Operating Temperature	+90 °C

RoHS

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-FLEX15-15x10	0.15	15.0	10.0 m	Black (BK)	710-00104
	0.15	15.0	10.0 m	Blue (BU)	710-00100
	0.15	15.0	10.0 m	Brown (BN)	710-00107
	0.15	15.0	10.0 m	Clear (CL)	710-00147
	0.15	15.0	10.0 m	Green (GN)	710-00103
	0.15	15.0	10.0 m	Green-Yellow (GNYE)	710-00106
	0.15	15.0	10.0 m	Grey (GY)	710-00108
	0.15	15.0	10.0 m	Orange (OG)	710-00110
	0.15	15.0	10.0 m	Red (RD)	710-00101
	0.15	15.0	10.0 m	Red (RD), Grey (GY), Yellow (YE), Green (GN), Blue (BU), Orange (OG), White (WH), Brown (BN), Black (BK), Green-Yellow (GNYE)	710-00146
	0.15	15.0	10.0 m	Violet (VT)	710-00109
	0.15	15.0	10.0 m	White (WH)	710-00105
	0.15	15.0	10.0 m	Yellow (YE)	710-00102

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



HelaTape Flex - Vinyl Electrical Tapes

HelaTape Flex 15 - All Purpose Vinyl Insulating Tape

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-FLEX15-19x20	0.15	19.0	20.0 m	Black (BK)	710-00155
	0.15	19.0	20.0 m	Blue (BU)	710-00151
	0.15	19.0	20.0 m	Brown (BN)	710-00158
	0.15	19.0	20.0 m	Green (GN)	710-00154
	0.15	19.0	20.0 m	Green-Yellow (GNYE)	710-00157
	0.15	19.0	20.0 m	Grey (GY)	710-00159
	0.15	19.0	20.0 m	Red (RD)	710-00152
	0.15	19.0	20.0 m	Violet (VT)	710-00160
	0.15	19.0	20.0 m	White (WH)	710-00156
	0.15	19.0	20.0 m	Yellow (YE)	710-00153
HTAPE-FLEX15-25x25	0.15	25.0	25.0 m	Black (BK)	710-00137
	0.15	25.0	25.0 m	Blue (BU)	710-00133
	0.15	25.0	25.0 m	Brown (BN)	710-00140
	0.15	25.0	25.0 m	Green (GN)	710-00136
	0.15	25.0	25.0 m	Green-Yellow (GNYE)	710-00139
	0.15	25.0	25.0 m	Grey (GY)	710-00141
	0.15	25.0	25.0 m	Red (RD)	710-00134
	0.15	25.0	25.0 m	Violet (VT)	710-00142
	0.15	25.0	25.0 m	White (WH)	710-00138
0.15	25.0	25.0 m	Yellow (YE)	710-00135	

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.