



PRODUCT-DETAILS

XT2N 160 TMA 40-400 4p F F

XT2N 160 TMA 40-400 4p F F



General Information	
Extended Product Type	XT2N 160 TMA 40-400 4p F F
Product ID	1SDA067035R1
EAN	8015644009410
Catalog Description	XT2N 160 TMA 40-400 4p F F
Long Description	C.BREAKER TMAX XT2N 160 FIXED FOUR-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMA R 40 I3=200...400 A

ABB EcoSolutions	
ABB EcoSolutions	Yes
ABB Site Meeting Group	UL 2799 Zero Waste To Landfill Validation available
Waste To Landfill Target	
End Of Life Disassembling Instructions	9AKK108468A2348
Environmental Product Declaration - EPD	9AKK108469A1856 9AKK108468A1891
Extended Product Lifetime	Product Modularity
Recyclability Rate of the Product acc. to EN45555	Design for Closing Resource Loops - Standard EN45555 - 55.70 %

---

### Material Compliance

---

REACH Declaration	9AKK108466A1425
RoHS Declaration	9AKK108466A1424
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
Toxic Substances Control Act - TSCA	9AKK108467A8326

---



---

### Environmental

---

Environmental Information	9AKK108467A6707
---------------------------	-----------------

---



---

### Ordering

---

Order Code US and Canada	XT2NE4040BFF000XXX
E-Number (Norway)	4309740
EAN	8015644009410
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

---



---

### Dimensions

---

Product Net Width	120 mm
Product Net Height	130 mm
Product Net Depth / Length	82.5 mm
Product Net Weight	1.6 kg

---



---

### Container Information

---

Package Level 1 Units	box 1 piece
Package Level 1 Width	130 mm
Package Level 1 Height	208 mm
Package Level 1 Depth / Length	145 mm
Package Level 1 Gross Weight	2.098 kg
Package Level 1 EAN	8015644009410

---



---

### Additional Information

---

Circuit Breaker Type to be Associated	Power Distribution
Product Main Type	SACE Tmax XT
Product Name	Moulded Case Circuit Breaker
Product Type	Automatic Circuit Breaker
Version	F
CAD Dimensional Drawing	1SDH002230A1002

---



---

### Technical

---

Connecting Capacity Main	Busbar 32.5..100 mm²
--------------------------	----------------------

---

Circuit	
Current Type	AC/DC
Electrical Durability	120 cycles per hour 8000 cycle
Mechanical Durability	240 cycles per hour 25000 cycle
Number of Poles	4P
Opening Time	CB with SOR 30 ms CB with UVR 30 ms
Order Multiple	1 piece
Power Loss	at Rated Operating Conditions per Pole 3.71 W
Rated Current ( $I_n$ )	40 A
Rated Frequency (f)	50 / 60 Hz
Rated Impulse Withstand Voltage ( $U_{imp}$ )	8 kV
Rated Instantaneous Short-Circuit Current Setting ( $I_s$ )	300...400 A
Rated Insulation Voltage ( $U_i$ )	1000 V
Rated Operational Voltage	690 V AC 500 V DC
Rated Service Short-Circuit Breaking Capacity ( $I_{cs}$ )	(220 V AC) 65 kA (230 V AC) 65 kA (240 V AC) 65 kA (380 V AC) 36 kA (415 V AC) 36 kA (440 V AC) 36 kA (500 V AC) 30 kA (525 V AC) 20 kA (690 V AC) 10 kA (250 V DC) 2 Poles in Series 36 kA (500 V DC) 3 Poles in Series 36 kA
Rated Ultimate Short-Circuit Breaking Capacity ( $I_{cu}$ )	(220 V AC) 65 kA (230 V AC) 65 kA (240 V AC) 65 kA (380 V AC) 36 kA (415 V AC) 36 kA (440 V AC) 36 kA (500 V AC) 30 kA (525 V AC) 20 kA (690 V AC) 10 kA (250 V DC) 2 Poles in Series 36 kA (500 V DC) 3 Poles in Series 36 kA
Rated Uninterrupted Current ( $I_u$ )	160 A
Rated Voltage ( $U_r$ )	690 V
Recommended Screw Driver	Main Circuit M6
Release	TMA
Release Type	TM
Setting Range	28...40 A
Short-Circuit Performance Level	N
Standards	IEC60947-2
Sub-type	XT2
Terminal Connection Type	Front
Terminal Type	Bolt
Tightening Torque	6 N·m

### Certificates and Declarations

ATEX Certificate	No certification needed
Data Sheet, Technical Information	1SDC210100D0206 1SDC210099D0206
Declaration of Conformity	9AKK106713A5901

- CE	
GL Certificate	1SDL000163R0093
LR Certificate	1SDL000163R0100
UL Certificate	No certification needed
VDE Certificate	No certification needed
Dimension Diagram	1SDH000721R0100
Mechanical Drawings	1SDH000721R0100
Wiring Diagram	1SDM000068R0001
Instructions and Manuals	1SDH000721R0001

---

### External Classifications and Standards

ETIM 9	EC000228 - Power circuit-breaker for trafo/generator/installation protection
ETIM 10	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
UNSPSC	39120000
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
eClass	V11.1 : 27370409

---

### Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT

