



**SAFETY DATA SHEET**  
SAPPHIRE HI-PRESSURE

Page: 1

Compilation date: 08/12/2014

Revision date: 05/02/2016

Revision No: 7

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** SAPPHIRE HI-PRESSURE

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** Lubricating Grease

**1.3. Details of the supplier of the safety data sheet**

**Company name:** ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

**Tel:** +44 (0) 113 232 2700

**Fax:** +44 (0) 113 232 2740

**Email:** [customer-service@rocol.com](mailto:customer-service@rocol.com)

**1.4. Emergency telephone number**

**Emergency tel:** +44 (0) 113 232 2600

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** This product has no classification under CLP.

**2.2. Label elements**

**Label elements:** This product has no label elements.

**2.3. Other hazards**

**PBT:** This product is not identified as a PBT/vPvB substance.

**Section 3: Composition/information on ingredients**

**3.2. Mixtures**

# SAFETY DATA SHEET

SAPPHIRE HI-PRESSURE

Page: 2

## Hazardous ingredients:

DISTILLATES (PETROLEUM), HYDROTREATED HEAVY NAPHTHENIC (NOTE L - < 3% DMSO EXTRACT)

EINECS	CAS	PBT / WEL	CLP Classification	Percent
265-097-6	64741-96-4	Substance with a Community workplace exposure limit.	-	30-50%

SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)

265-166-0	64742-62-7	Substance with a Community workplace exposure limit.	-	30-50%
-----------	------------	--	---	--------

SODIUM NITRITE

231-555-9	7632-00-0	-	Ox. Sol. 3: H272; Acute Tox. 3: H301; Aquatic Acute 1: H400	<1%
-----------	-----------	---	---	-----

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes.

**Ingestion:** Wash out mouth with water.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** No symptoms.

### 4.3. Indication of any immediate medical attention and special treatment needed

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Use water spray to cool containers. Suitable extinguishing media for the surrounding fire should be used.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details.

[cont...]

# SAFETY DATA SHEET

SAPPHIRE HI-PRESSURE

Page: 3

## 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers.

## 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Transfer to a closable, labelled salvage container for disposal by an appropriate method.

## 6.4. Reference to other sections

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area.

**Suitable packaging:** Must only be kept in original packaging.

### 7.3. Specific end use(s)

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**DISTILLATES (PETROLEUM), HYDROTREATED HEAVY NAPHTHENIC (NOTE L - < 3% DMSO EXTRACT)**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	5 mg/m <sup>3</sup>	10 mg/m <sup>3</sup>	-	-

**SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)**

EU	-	5 mg/m <sup>3</sup>	-	-
----	---	---------------------	---	---

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Respiratory protection:** Respiratory protection not normally required.

**Hand protection:** Protective gloves.

**Eye protection:** Safety glasses with side-shields.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Paste

[cont...]

# SAFETY DATA SHEET

SAPPHIRE HI-PRESSURE

Page: 4

**Colour:** Blue-black

**Odour:** Odourless

**Evaporation rate:** Negligible

**Oxidising:** Non-oxidising (by EC criteria)

**Solubility in water:** Insoluble

**Viscosity:** Highly viscous

**Melting point/range°C:** > 200

**Flash point°C:** > 200

**Autoflammability°C:** > 200

**Relative density:** < 1

## 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

### 10.4. Conditions to avoid

**Conditions to avoid:** Heat.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong reducing agents.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Hazardous ingredients:**

#### SODIUM NITRITE

ORL	MUS	LD50	175	mg/kg
ORL	RAT	LD50	180	mg/kg
SCU	RAT	LD50	96600	µg/kg

**Toxicity values:** No data available.

### Symptoms / routes of exposure

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** No symptoms.

[cont...]

**SAFETY DATA SHEET**  
SAPPHIRE HI-PRESSURE

Page: 5

**Section 12: Ecological information**

**12.1. Toxicity**

**Ecotoxicity values:** No data available.

**12.2. Persistence and degradability**

**Persistence and degradability:** Only slightly biodegradable.

**12.3. Bioaccumulative potential**

**Bioaccumulative potential:** No bioaccumulation potential.

**12.4. Mobility in soil**

**Mobility:** Non-volatile. Absorbed only slowly into soil.

**12.5. Results of PBT and vPvB assessment**

**PBT identification:** This product is not identified as a PBT/vPvB substance.

**12.6. Other adverse effects**

**Section 13: Disposal considerations**

**13.1. Waste treatment methods**

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

**Section 14: Transport information**

**Transport class:** This product does not require a classification for transport.

**Section 15: Regulatory information**

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

**15.2. Chemical Safety Assessment**

**Section 16: Other information**

**Other information**

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

Compiled in accordance with REACH.

**Phrases used in s.2 and s.3:** H272: May intensify fire; oxidiser.

H301: Toxic if swallowed.

H400: Very toxic to aquatic life.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.

