




VideoInspector XXL

Professional video inspection for simple visual inspection of areas that are difficult to access - Long camera unit perfect for long-distance use

The professional video inspection is ideal for precise problem localisation behind or in objects, walls, pipes and cavities. The camera head and probe are waterproof and resistant to diesel, petrol, motor oil, AdBlue®, ethanol and sea water, making the device extremely versatile. Thanks to the long camera unit, the product is especially suited for deployment at long distances. Further benefits include the top quality LED object lighting and the magnetic stand for setting up the base unit. The true colour reproduction provides an extremely realistic image.

- Effective problem localisation behind or in objects, walls, pipes, cavities
- Long camera unit for use over long distances
- Waterproof camera head and probe: also resistant to diesel, petrol, motor oil, AdBlue®, ethanol and sea water (salinity 28%)
- Powerful object lighting thanks to 8 high-performance LEDs
- User has both hands free to work thanks to the magnetic stands on the camera unit
- Device fits well in the hand due to ergonomic design
- Various views available on the monitor through rotation and mirroring



TECHNICAL DATA

Diameter Camera Head	7.9 mm
Camera Resolution	1280 x 720 pixels
Field of View (FOV)	80°
Depth of Focus (DOF)	3 ... 8 cm
Screen Type	3,5"
Display Resolution	640 x 480 pixels
Image Format	JPEG
Length of Probe	5 m
Illumination	4 brightness levels
Digital Zoom	2x digital zoom in 10% increments
Memory	Micro-SD memory card up to 32 GB
Ports	USB type C
Power Supply	Li-ion battery pack 3.7V / 2.8Ah USB type C 5V / 2A
Dimensions (W x H x D)	108 mm x 260 mm x 110 mm x (incl. holder)
Weight	1070 g (incl. battery pack)



SCOPE OF DELIVERY



Item No. 092.928A GTIN (EAN) 4021563737796 SU 1