



Main

Range of product	Harmony XVB7
Product or component type	Light module
Device composition	Beacon lens
Device short name	XVB7
Mounting diameter	70 Mm
Signalling type	Steady
Light source	LED, yellow
Material	PC (polycarbonate)
Net weight	0.094 Kg
Mounting position	Upright/Inverted

Complementary

Service life in hours	50000 H
[Ue] rated operational voltage	24 V AC/DC
Rated operational voltage limits	21.6...26.4 V AC/DC
Current consumption	35 mA at 24 V AC 40 mA at 24 V DC
Inrush current	0.5 A
Electrical shock protection class	Class II
[Ui] rated insulation voltage	50 V
[Uimp] rated impulse withstand voltage	0.5 KV

Environment

Pollution degree	2
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C
IP degree of protection	IP66
NEMA degree of protection	Type 4/4X/12/13 indoor use only
Vibration resistance	6 gn, amplitude = +/- 0.5 mm (f = 10...500 Hz)in operation
Shock resistance	30 gn (duration = 6 ms) for in operation

Standards	UL 60947-5-1 IEC 60947-5-1 CSA C22.2 No 60947-5-1
Product certifications	cULus[RETURN]CCC[RETURN]RCM[RETURN]UKCA[RETURN]CE

Ordering and shipping details

Category	US10CS222612
Discount Schedule	OCS2
GTIN	3606487129547
Returnability	Yes
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.500 Cm
Package 1 Width	7.300 Cm
Package 1 Length	7.500 Cm
Package 1 Weight	92.000 G
Unit Type of Package 2	S02
Number of Units in Package 2	30
Package 2 Height	15 Cm
Package 2 Width	30 Cm
Package 2 Length	40 Cm
Package 2 Weight	3.094 Kg

Offer Sustainability

Recyclability potential, in %	89
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is k
Total lifecycle Carbon footprint	11 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.9889988542101489
Carbon footprint of the manufacturing phase [A1 to A3]	1 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.03290387027852485
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.0005043411599917425
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	10.189760279105856
Carbon footprint of the use phase [B2, B3, B4, B6]	10 kg CO2 eq.
Mercury free	Yes
Sustainable packaging	No
Carbon footprint of the end-of-life phase [C1 to C4]	0.09019369433860897
Carbon footprint of the end-of-life phase [C1 to C4]	0.1 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile
Total lifecycle Carbon footprint	11
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
REACH Regulation	Reference contains Substances of Very High Concern above the threshold ↗
EU RoHS Directive	Compliant By Exemption ↗
End of life manual availability	End Of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and neve

Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **Commercialised**