

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: JENOLITE RUST REMOVER AND PREVENTER (THIXOTROPIC)

Product code: 301613

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Rust remover.

1.3. Details of the supplier of the safety data sheet

Company name: Jenolite UK Ltd
Chater Lea Buildings
Letchworth
Hertfordshire
SG6 1WT
Tel: 01462 480764
Email: Sales@Jenolite.net

1.4. Emergency telephone number

Emergency tel: 01462 480764
(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Acute Tox. 4: H302; Eye Irrit. 2: H319; Skin Irrit. 2: H315

Most important adverse effects: Harmful if swallowed. Causes skin irritation. Causes serious eye irritation.

2.2. Label elements

Label elements:

Hazard statements: H302: Harmful if swallowed.
H315: Causes skin irritation.
H319: Causes serious eye irritation.

Hazard pictograms: GHS07: Exclamation mark



Signal words: Warning

Precautionary statements: P264: Wash exposed skin thoroughly after handling.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P301+P312: IF SWALLOWED: Call a POISON CENTRE or doctor if you feel unwell.

SAFETY DATA SHEET

JENOLITE RUST REMOVER AND PREVENTER (THIXOTROPIC)

Page: 2

P302+P352: IF ON SKIN: Wash with plenty of water.

P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P321: Specific treatment (see information on this label)

P330: Rinse mouth.

P332+P313: If skin irritation occurs: Get medical advice/attention.

P337+P313: If eye irritation persists: Get medical advice/attention.

P501: Dispose of contents/container to comply with Local, National and International requirements.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

ORTHOPHOSPHORIC ACID

EINECS	CAS	PBT / WEL	CLP Classification	Percent
231-633-2	7664-38-2	-	Skin Corr. 1B: H314	10-30%

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water. Do not induce vomiting. If conscious, give half a litre of water to drink immediately. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be soreness and redness of the mouth and throat. Inhalation of fumes from the stomach may cause symptoms similar to direct inhalation.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

[cont...]

SAFETY DATA SHEET

JENOLITE RUST REMOVER AND PREVENTER (THIXOTROPIC)

Page: 3

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid. If outside keep bystanders upwind and away from danger point.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Polyethylene. Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

[cont...]

SAFETY DATA SHEET

JENOLITE RUST REMOVER AND PREVENTER (THIXOTROPIC)

Page: 4

8.1. Control parameters

Hazardous ingredients:

ORTHOPHOSPHORIC ACID...100%

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1 mg/m ³	2 mg/m ³	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Pink

Odour: Odourless

Oxidising: Oxidising (by EC criteria)

Solubility in water: Soluble

Kinematic viscosity: > 20 poise

Viscosity test method: Kinematic viscosity in 10⁻⁶ m²/s at 40°C (ISO 3104/3105)

Boiling point/range°C: > 100

Flash point°C: >93

Relative density: 1.1

pH: <2

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

[cont...]

SAFETY DATA SHEET

JENOLITE RUST REMOVER AND PREVENTER (THIXOTROPIC)

Page: 5

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values:

Route	Species	Test	Value	Units
VAPOURS	HMN	TCLO	100	mg/m ³
ORAL	RAT	LD50	1530	mg/kg
DERMAL	RBT	LD50	2740	mg/kg

Hazardous ingredients:

ORTHOPHOSPHORIC ACID...100%

ORL	RAT	LD50	1530	mg/kg
-----	-----	------	------	-------

Relevant hazards for product:

Hazard	Route	Basis
Acute toxicity (ac. tox. 4)	ING	Hazardous: calculated
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be soreness and redness of the mouth and throat. Inhalation of fumes from the stomach may cause symptoms similar to direct inhalation.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

[cont...]

SAFETY DATA SHEET

JENOLITE RUST REMOVER AND PREVENTER (THIXOTROPIC)

Page: 6

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values:

Species	Test	Value	Units
Mosquito/Fish	TLM/24-96hrs in Turb	138	mg/l

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Disposal of packaging: Arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN3264

14.2. UN proper shipping name

Shipping name: CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S.
(ORTHOPHOSPHORIC ACID)

14.3. Transport hazard class(es)

Transport class: 8

14.4. Packing group

Packing group: III

[cont...]

SAFETY DATA SHEET

JENOLITE RUST REMOVER AND PREVENTER (THIXOTROPIC)

Page: 7

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H302: Harmful if swallowed.

H314: Causes severe skin burns and eye damage.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.