

RIF-T3-24UC - Timer module



2902647

<https://www.phoenixcontact.com/gb/products/2902647>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in module for extending a relay module to create a timer relay, 3 time functions, 4 time ranges, for mounting on RIF-1, RIF-2, RIF-3, and RIF-4, input voltage: 12 V DC ... 24 V DC

Commercial data

Item number	2902647
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	DK6545
Product key	DK6545
Catalog page	Page 258 (C-5-2019)
GTIN	4046356668880
Weight per piece (including packing)	5.63 g
Weight per piece (excluding packing)	5.1 g
Customs tariff number	85363010
Country of origin	DE

RIF-T3-24UC - Timer module



2902647

<https://www.phoenixcontact.com/gb/products/2902647>

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Plug-in module
Product family	RIFLINE complete

Insulation characteristics: Air clearances and creepage distances in a circuit

Insulation	Basic insulation
Overvoltage category	I
Pollution degree	2

Electrical properties

Setting accuracy	3 % (of scale end value)
Nominal voltage U_N	24 V AC/DC
Repeat accuracy	1 %

Air clearances and creepage distances in a circuit

Rated insulation voltage	50 V DC
Rated surge voltage	0.4 kV

Input data

Nominal input voltage U_N	24 V DC (AC operation only permitted for RIF-1)
Input voltage range in reference to U_N	0.4 ... 1.2
Mains frequency	50 Hz 60 Hz
Status display	LED (yellow)
Protective circuit	Varistor
Surge voltage protection	> 56 V

Output data

Limiting continuous current	≤ 250 mA (Relay coil current)
Voltage drop at max. limiting continuous current	< 100 mV

Dimensions

Width	13 mm
Height	12 mm
Depth	35 mm

Environmental and real-life conditions

RIF-T3-24UC - Timer module



2902647

<https://www.phoenixcontact.com/gb/products/2902647>

Ambient conditions

Ambient temperature (operation)	-25 °C ... 50 °C (RIF-1, AC coil, 2 changeover contacts at 6 A)
	-25 °C ... 50 °C (RIF-1, DC coil, 2 changeover contacts at 5 A)
	-25 °C ... 40 °C (RIF-2, DC coil, 2 changeover contacts at 8 A)
	-25 °C ... 40 °C (RIF-2, DC coil, 4 changeover contacts at 5 A)
	-25 °C ... 40 °C (RIF-3, DC coil, 3 changeover contacts at 6.75 A)
	-25 °C ... 40 °C (RIF-3, DC coil, 2 changeover contacts at 8 A)
	-25 °C ... 35 °C (RIF-4, DC coil, 3 changeover contacts at 8 A)
	-25 °C ... 25 °C (RIF-4, DC coil, 3 N/O contacts at 8 A)
Ambient temperature (storage/transport)	-25 °C ... 85 °C

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

Corrosive gas test

Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

Standards and regulations

Air clearances and creepage distances in a circuit


Standards/regulations	IEC 60947-5-1
-----------------------	---------------

Mounting

Assembly note	Can be inserted into relay base
Mounting position	any


Drawings

Diagram




With switch-on delay

Diagram



With passing make contact

Diagram



Flasher/pulse generator


RIF-T3-24UC - Timer module

2902647

<https://www.phoenixcontact.com/gb/products/2902647>



Circuit diagram



RIF-T3-24UC - Timer module



2902647

<https://www.phoenixcontact.com/gb/products/2902647>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2902647>



CSA

Approval ID: 76787



UL Recognized

Approval ID: FILE E 113228



EAC

Approval ID: RU*DE.*08.B.01536/19

DNV

Approval ID: TAA000018V

RIF-T3-24UC - Timer module



2902647

<https://www.phoenixcontact.com/gb/products/2902647>

Classifications

ECLASS

ECLASS-13.0	27371692
-------------	----------

ETIM

ETIM 9.0	EC002586
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

RIF-T3-24UC - Timer module



2902647

<https://www.phoenixcontact.com/gb/products/2902647>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk