



**Part Number :** [1200680211](#)  
**Product Description :** Ultra-Lock (M12) to Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 0.34mm<sup>2</sup> TPE Cable, 0.30m Length  
**Series Number :** 120068  
**Status :** Active  
**Product Category :** Industrial Tees and Splitters  
**Engineering Number :** 884A31K05M003




Documents & Resources

Drawings  
[1200680211\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	Ultra-Lock (M12) to Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 0.34mm <sup>2</sup> TPE Cable, 0.30m Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Splitter - In-line
UPC	78678883476

### Agency

CSA	LR6837
UL	E152210

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

### Physical

Color - Cable Jacket	Yellow
Drop Connector	N/A
Drop Gender	N/A
Keyway	Single
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Male
Leg 1 Length	0.30m
Leg 2 Length	0.30m

Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Net Weight	55.538/g
Poles	3 Female/4 Male
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-30°C to +70°C

---



---

This document was generated on Mar 27, 2025