

Surge protection device - TTC-6P-2X1-F-12DC-PT-I - 2908206


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Surge protection, consisting of protective plug and base element, with integrated status indicator for two signal wires with common reference potential, e.g., Digital IN/OUT. Indirect grounding via gas-filled surge arrester.



Key Commercial Data

Packing unit	1
GTIN	 4 055626 282909
GTIN	4055626282909

Technical data

Dimensions

Height	105.8 mm
	105.8 mm
Width	6.2 mm
Depth	100 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Degree of protection	IP20

General

Housing material	PBT
Flammability rating according to UL 94	V-0
Color	traffic grey A RAL 7042
	light gray RAL 7035
Mounting type	DIN rail: 35 mm
Design	DIN rail module, two-section, divisible

Surge protection device - TTC-6P-2X1-F-12DC-PT-I - 2908206

Technical data

General

Direction of action	Line-Line & Line-Signal Ground/Shield & optional Signal Ground/Shield-Earth Ground
---------------------	--

Protective circuit

IEC test classification	C1
	C2
	C3
	D1
Nominal voltage U_N	12 V DC
Maximum continuous voltage U_C	15 V DC
Rated current	600 mA (56 °C)
Operating effective current I_C at U_C	$\leq 100 \mu\text{A}$
Residual current I_{PE}	$\leq 1 \mu\text{A}$
Nominal discharge current I_n (8/20) μs (core-earth)	5 kA
Nominal discharge current I_n (8/20) μs (core-GND)	5 kA
Pulse discharge current I_{imp} (10/350) μs (core-ground)	0.5 kA
Pulse discharge current I_{imp} (10/350) μs (core-GND)	0.5 kA
Total discharge current I_{total} (8/20) μs	10 kA
Voltage protection level U_p (core-ground)	$\leq 750 \text{ V}$ (C1 - 1 kV/500 A)
	$\leq 750 \text{ V}$ (C2 - 10 kV / 5 kA)
	$\leq 1.2 \text{ kV}$ (C3 - 25 A)
	$\leq 1.3 \text{ kV}$ (C3 - 100 A)
Voltage protection level U_p (core-GND)	$\leq 145 \text{ V}$ (C1 - 1 kV/500 A)
	$\leq 285 \text{ V}$ (C2 - 10 kV / 5 kA)
	$\leq 25 \text{ V}$ (C3 - 25 A)
	$\leq 30 \text{ V}$ (C3 - 100 A)
Voltage protection level U_p static (core-ground)	$\leq 750 \text{ V}$ (C1 - 1 kV/500 A)
	$\leq 750 \text{ V}$ (C2 - 10 kV / 5 kA)
Voltage protection level U_p static (core-GND)	$\leq 35 \text{ V}$ (C1 - 1 kV/500 A)
	$\leq 105 \text{ V}$ (C2 - 10 kV / 5 kA)
Response time t_A (core-earth)	$\leq 1 \text{ ns}$
	$\leq 100 \text{ ns}$
Input attenuation a_E , asym.	typ. 0.3 dB ($\leq 140 \text{ kHz} / 150 \Omega$)
Cut-off frequency f_g (3 dB), asym. (GND) in 150 Ohm system	typ. 440 kHz
Capacity (Core-GND)	typ. 5.2 nF
Resistance in series	1.65 $\Omega \pm 20 \%$
Surge protection fault message	optical
Max. required back-up fuse	630 mA (FF)
Impulse durability (conductor-ground)	C1 - 1 kV/500 A
	C2 - 10 kV/5 kA
	C3 - 100 A

Surge protection device - TTC-6P-2X1-F-12DC-PT-I - 2908206

Technical data

Protective circuit

	D1 - 500 A
Impulse durability (conductor-GND)	C1 - 1 kV/500 A
	C2 - 10 kV/5 kA
	C3 - 100 A
	D1 - 500 A
Pulse reset time (conductor-ground)	≤ 30 ms
Pulse reset time (conductor-GND)	≤ 30 ms

Connection data

Connection method	Push-in connection
Connection method IN	Push-in connection
Connection method OUT	Push-in connection
Stripping length	8 mm
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section solid	0.2 mm ² ... 4 mm ²
Conductor cross section AWG	24 ... 12

Standards and Regulations


Standards/specifications	IEC 61643-21 2000 + corrigendum 2001 + A1:2008, modified + A2:2012
	EN 61643-21 2001 + A1:2009 + A2:2013

Drawings


Pictogram



Diagram



Dimensional drawing



Circuit diagram

