



- 14 pin plug-inAnalogue Dial DisplayOn Delay timer



ENGLISH






ENGLISH

RS Sto	ock No	179-2962	179-2963	179-2964	179-2965
Specification	n				
Supply Voltage		230Vac			
Operating Voltage Range		Rated voltage 85-110%			
Power consumption		3.5W			
Timing Function		On Delay			
Timing Range		0.1min – 3min	0.2min – 5min	0.5min – 10min	1min – 30min
Configuration Contact Rated Current		4PDT (4C)			
	AC-1	3A @ 250VAC (p.f. =1)			
Repetitive Error		±2% (FS max.)			
Setting Error		±5% (FS max.)			
Voltage Error		±2% (FS max.)			
Temperature Error		±2% (FS max.)			
Resetting Time		Min.time: 0.2 sec			
Insulation resistance		100MW (DC500V)			
Dielectric strength		Between current-carrying and Non-current-carrying parts 2000V 50/60Hz min			
		Between control output terminals and operating circuit1500V 50/60Hz min			
		Between contacts 1000V 50/60Hz min			
Vibration Resisance	Destruction	10~55Hz with 0.75mm single amplitude each in 3directions for 2 hours each			
	Malfunction	10~55Hz with 0.5mm single amplitude each in 3 directions for 10 minutes each			
Shock Resistance	Destruction	30G			
	Malfunction	10G			
Life Expectancy	Electrical Life	>10 ⁷ (under no load, at 1,800 operations/hour)			
	Mechanical Life	>10 ⁵			
Ambient temperature		-10°C~55°C			
Ambient humidity		35~85%RH			
Mounting		14 Plug-in			
Unit Weight		Approx.60g			
Certification		C E ROHS			






ENGLISH




Connection Diagram



Timing Diagram

Power 13-14 Time-limit contact (NC) 9-1, 10-2, 11-3, 12-4 Time-limit contact (NO) 9-5, 10-6, 11-7, 12-8 Power indicator

Output indicator



NOTE: t:set time, Rt: reset time