

Productname : Alu Paste
Ref.Nr.: BDS001448_3_20130806

Creationdate : 06.08.13 Version : 2.0
Replaces: BDS001448_20130619

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Alu Paste
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Anti-seize lubricant

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Laurinkatu 57 A 23 B, 08100 Lohja	+358/(19)32.921	+358/(19)383.676
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptongatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1
Extremely flammable aerosol.
Pressurised container: May burst if heated.

Health: Skin irritation, category 2



Productname :	Alu Paste	Creationdate :	06.08.13 Version : 2.0
Ref.Nr.:	BDS001448_3_20130806	Replaces:	BDS001448_20130619

	Causes skin irritation.
	Specific target organ toxicity - single exposure, category 3
	May cause drowsiness or dizziness.
Environment:	Hazardous to the aquatic environment, chronic category 2
	Toxic to aquatic life with long lasting effects.
Other hazards :	None

Classification according to 67/548/EEC or 1999/45/EC:

Health:	R66: Repeated exposure may cause skin dryness or cracking. R67: Vapours may cause drowsiness and dizziness.
Physical:	EXTREMELY FLAMMABLE
Environment:	R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements**Labelling according to Regulation (EC) No 1272/2008**

Product identifier:	Contains: hydrocarbons
----------------------------	---------------------------

Hazard pictogram(s):

Signal word:	Danger
---------------------	--------

Hazard statement(s):	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H315 : Causes skin irritation. H336 : May cause drowsiness or dizziness. H411 : Toxic to aquatic life with long lasting effects.
-----------------------------	---

Precautionary statement(s):	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P261 : Avoid breathing dust/fume/gas/mist/vapours/spray. P271 : Use only outdoors or in a well-ventilated area. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.
------------------------------------	---

Supplemental Hazard information:	None
---	------

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients**3.1. Substances****CRC Industries Europe bvba**

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

Productname : Alu Paste
Ref.Nr.: BDS001448_3_20130806

Creationdate : 06.08.13 Version : 2.0
Replaces: BDS001448_20130619

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	25-50	F+	12	K,G
pentane	109-66-0	203-692-4	10-25	F+,Xn,N	12-51/53-65-66-67	A
Naphtha (petroleum), hydrotreated light	64742-49-0	931-254-9	10-25	F,Xn,N	11-38-51/53-65-67	B,P
aluminium powder (stabilized)	7429-90-5	231-072-3	1-5	F	11-15	A
Naphtha (petroleum), hydrodesulfurized heavy	64742-82-1	265-185-4	<1	Xn,N	10-51/53-65-66-67	B,P
Solvent naphtha (petroleum), light arom. (benzene<0.1%)	64742-95-6	265-199-0	<1	Xn,N	10-37-51/53-65-66-67	B,P

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

P : not classified as carcinogen, less than 0.1% w/w benzene (Einecs-nr. 200-753-7)

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	-	68512-91-4	270-990-9	25-50	Press. Gas, Flam. Gas 1	H280,H220	K,G
pentane	01-2119459286-30	109-66-0	203-692-4	10-25	Flam. Liq. 2, Asp. Tox. 1, STOT SE 3, Aquatic Chronic 2	H225,H304,H336,H411	A
Naphtha (petroleum), hydrotreated light	01-2119484651-34	64742-49-0	931-254-9	10-25	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225,H315,H336,H304,H411	B,P
aluminium powder (stabilized)		7429-90-5	231-072-3	1-5	Water-react. 2, Flam. Sol. 1	H261,H228	A

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

P : not classified as carcinogen, less than 0.1% w/w benzene (Einecs-nr. 200-753-7)

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

Productname : Alu Paste
Ref.Nr.: BDS001448_3_20130806

Creationdate : 06.08.13 Version : 2.0
Replaces: BDS001448_20130619

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water If eye irritation persists: Get medical advice/attention.
Contact with skin :	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	Irritating to skin Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO, CO₂

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures



Productname : Alu Paste
Ref.Nr.: BDS001448_3_20130806

Creationdate : 06.08.13 Version : 2.0
Replaces: BDS001448_20130619

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep out of reach of children.

7.3. Specific end use(s)

Anti-seize lubricant

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method
EU established exposure limits:		



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

Productname : Alu Paste
Ref.Nr.: BDS001448_3_20130806

Creationdate : 06.08.13 Version : 2.0
Replaces: BDS001448_20130619

pentane	109-66-0	TWA	1000 ppm
National established exposure limits, United Kingdom			
pentane	109-66-0	TWA	600 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)
hands and skin :	Wear suitable protective gloves against chemicals (nitrile)
eyes :	Wear safety goggles.
Environmental protection:	Avoid release to the environment. Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state :	Propane/butane propelled liquid.
colour :	Grey.
odour :	Characteristic odor.
pH :	Not applicable.
Boiling point/range :	Not available.
Flash point :	< 0 °C
Evaporation rate :	Not available.
Explosion limits : upper limit :	Not available.
lower limit :	Not available.
Vapour pressure :	Not available.
Relative density :	0.731 g/cm ³ (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	> 200 °C
Viscosity :	Not available.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose



Productname : Alu Paste
Ref.Nr.: BDS001448_3_20130806

Creationdate : 06.08.13 Version : 2.0
Replaces: BDS001448_20130619

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Irritating to skin
Eye contact :	May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
pentane	109-66-0	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 3000 mg/kg
Naphtha (petroleum), hydrodesulfurized heavy	64742-82-1	LD50 oral rat	> 2000 mg/kg
Naphtha (petroleum), hydrotreated light	64742-49-0	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 3000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 2
Toxic to aquatic life with long lasting effects.



Productname : Alu Paste
Ref.Nr.: BDS001448_3_20130806

Creationdate : 06.08.13 Version : 2.0
Replaces: BDS001448_20130619

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
Naphtha (petroleum), hydrodesulfurized heavy	64742-82-1	IC50 algae	1 - 10 mg/l
		LC50 fish	10 - 100 mg/l
		EC50 daphnia	10 - 100 mg/l
Naphtha (petroleum), hydrotreated light	64742-49-0	IC50 algae	55 mg/l
		LC50 fish	> 1 mg/l
		EC50 daphnia	3.87 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

Contaminated packaging : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information**14.1. UN number**

UN-number : 1950



Productname : Alu Paste
Ref.Nr.: BDS001448_3_20130806

Creationdate : 06.08.13 Version : 2.0
Replaces: BDS001448_20130619

14.2. UN proper shipping name

Proper shipping name: AEROSOLS (naphta, pentane)

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally
hazardous: Yes
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally
hazardous: Yes

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
Regulation (EC) No 1907/2006 (REACH)
EU-directive 99/45/EC
Regulation (EC) No 1272/2008 (CLP)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information



Productname : Alu Paste
Ref.Nr.: BDS001448_3_20130806

Creationdate : 06.08.13 Version : 2.0
Replaces: BDS001448_20130619

- *Explanation risk-phrases:
- R10: Flammable.
 - R11: Highly flammable.
 - R12: Extremely flammable.
 - R15: Contact with water liberates extremely flammable gases.
 - R37: Irritating to respiratory system.
 - R38: Irritating to skin.
 - R65: Harmful: may cause lung damage if swallowed.
 - R66: Repeated exposure may cause skin dryness or cracking.
 - R67: Vapours may cause drowsiness and dizziness.
 - R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- *Explanation hazard statements:
- H220 : Extremely flammable gas.
 - H225 : Highly flammable liquid and vapour.
 - H228 : Flammable solid.
 - H261 : In contact with water releases flammable gases.
 - H280 : Contains gas under pressure; may explode if heated.
 - H304 : May be fatal if swallowed and enters airways.
 - H315 : Causes skin irritation.
 - H336 : May cause drowsiness or dizziness.
 - H411 : Toxic to aquatic life with long lasting effects.

REVISIONS IN CHAPTRE : 2.2. Label elements

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.