

Product data sheet

Specifications



Repacked single phase relay,
Harmony Solid State Modular
Relays, 6A, DIN rail mount, DC
switching, input 4 to 32V DC, output
1 to 60V DC

SSM1D26BDW



This repacked option saves 0.333 over the
standard condition

Main

Range of product	Harmony Solid State Relays
Device short name	SSM
Product or component type	Modular DIN rail relay
Number of channels	1
Number of phases	1 phase
Output switching mode	DC switching

Complementary

Mounting support	Symmetrical DIN rail
[In] rated current	6 A
Output voltage	1...60 V DC
[Uc] control circuit voltage	4...32 V DC
Tightening torque	0.5...0.8 N.m for input 0.5...0.8 N.m for output
Connections - terminals	Screw terminals: 1 x 0.3...1 x 1.5 mm ² , (AWG 22...AWG 16) for input Screw terminals: 1 x 0.3...1 x 2.5 mm ² , (AWG 22...AWG 14) for output
maximum capacitance	10 pF for input/output
Insulation resistance	1000 MOhm at 500 V DC
Local signalling	LED (green) for input status
Minimum switching voltage	4 V DC turn-on
Maximum switching voltage	1 V DC turn-off
input current	8...11 mA
Solid state output type	Mosfet output DC switching
Load current	0.0025...6 A
transient overvoltage	60 V
Surge current	60 A for 10 ms
Maximum voltage drop	<0.6 V on-state
Resistance	0.1 Ohm on-state
Maximum leakage current	0.1 mA off-state

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Response time	0.6 ms (turn-on) 0.3 ms (turn-off)
Overvoltage category	III
Width	11 mm
Height	90.3 mm
test button	Without test button
Depth	83.7 mm
Product weight	0.05 kg

Environment

Flame retardance	V0 conforming to UL 94
Dielectric strength	4 kV DC for input/output 4 kV DC for input or output to case
Pollution degree	2
Standards	IEC 61000 IEC 62314 IEC 60950-1
Product certifications	UL CSA
Marking	CE
IP degree of protection	IP20
Ambient air temperature for operation	-30...80 °C
Ambient air temperature for storage	-30...100 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	9.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	56.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.305 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Lower carbon footprint	0.3 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.7 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	33 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
REACH Regulation	Reference contains Substances of Very High Concern above the threshold


Use Longer

Lifetime extension	
Repair	No

Image of product / Alternate images

Alternative












Image of product in real life situation

